







NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
- THREADED SPACER CLIPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\varnothing 3.1 \pm 0,1$; PCB THICKNESS 2,3mm
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- P.C.B. HOLE DRILLINGS ON SHEET 2
- CONNECTOR IS PART MARKED: **DSS3XPRAA15X CONEC ABC**

Directive 2002/95/EC
"RoHS"
Compliant


APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
						dim. in mm
				date	name	
				drawn	16.12.09	Lehmenkühler
				appd.	16.12.09	Kühle
				norm		
				d-old		
a	Origin					
rev.	description	date	name			

scale: 2:1 (5:1)	
material: SEE NOTES	
title: D-SUB MALE 25pos. SOLDER PIN STRAIGHT with threaded spacer clip	
dwg no: 16K1A2574-NA	Inventor 10
DIN-A3	
sh: 1	
part no: DSS3XPRAA15X North American Version	



PCB TOP SIDE

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance				scale: 2:1	
DO NOT ALTER CAD DRAWING BY HAND				date		name		material: SEE SHEET 1	
a				16.12.		Lehmenkühler		title:	
rev.				16.12.		Kühle		P.C.B. HOLE DRILLINGS	
description				norm				D-SUB MALE 25pos. SOLDER PIN	
date				d-old				with threaded spacer clip	
name								dwg no: Inventor 10	
								DIN-A3	
								sh: 2	
								part no: SEE SHEET 1	

