






PRODUCT NUMBER	PITCH
YK504xx0x0J0G	9.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT:
 WITHSTAND VOLTAGE:
 INSULATION RESISTANCE:
 OPERATING TEMPERATURE RANG:
 SCREW TORQUE VALUE:
 WIRE RANGE:
 1) HOUSING:
 2) TERMINAL:
 3) TERMINAL SCREWS:
 APPROVAL: US

300 V, 20 A
 AC 2000 V/Min
 1000 MΩ OR MORE AT DC 500 V
 -40 °C ~ +115 °C
 12 Lb-In.
 22 - 12AWG
 THERMOPLASTIC, UL 94 V-0 BLACK
 BRASS, 0.8t
 STEEL, M3.5

DIMENSION

Dim A	N×9.5±3.0
Dim B	(N-1)×9.5

N=Number of poles

Poles	Tolerance
2p-4p	±0.20
5p-10p	±0.30
11p-24p	±0.40
25p-30p	±0.60

PART NO.: YK 504xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles
 ...
 30 30 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface	tolerance	projection	product family		
ltr	ecn	no	dr	date	ASME Y14.5 ✓	ASME Y14.5	TERMINAL BLOCK		
					tolerances unless otherwise specified		title		
					angles	X.±0.5	TERMINAL BLOCK		
					dr	X.X±0.3	BARRIER TYPE		
					engr	X.XX±0.1	scale		
					chr	EVAN LU 061414	dwg no		
					appd	EVAN LU 061414	YK504xx0x0J0G		
						HANKE FENG 061414	sheet 1 of 1		
						SHI JUN 061414	size		
							A4		
							type		
							CUSTOMER Drawing		
sheet index	revision	A							
	sheet	1							