




Part Number : [734151061](#)
Product Description : MCX Jack, Straight, PCB
Receptacle, Edge Mount, Brass Body, Gold (Au) Plating,
Tape and Reel, 50 Ohms
Series Number : 73366
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734151061_sd.pdf](#)

3D Models and Design Files


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Straight, PCB Receptacle, Edge Mount, Brass Body, Gold (Au) Plating, Tape and Reel, 50 Ohms
Application	RF
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	822350648714

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.141/g
Orientation	Straight
Packaging Type	Embossed Tape on Reel
Panel Mount	No

Panel Mount Method	N/A
PCB Mounting	Edge Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	1
Max-Temp	260

This document was generated on Sep 17, 2025