

**Part Number :** 1202340001
**Product Description :** Brad M23 Power Connector, Front Panel-Mount Receptacle, Straight Female Flange Mount 4xØ 3.20mm, Crimp Contacts, 6 (5+PE) Poles
**Series Number :** 120234
**Status :** Obsolete
**Product Category :** Industrial Connectors
**Engineering Part Number :** KRP6G00-103

## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Product not active |
| China RoHS | Product not active |
| EU ELV | Product not active |
| Low-Halogen Status | Product not active |
| REACH SVHC | Product not active |
| EU RoHS | Product not active |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

Obsolete

Downloaded from Arrow.com.

## General

| | |
|---|---|
| Status | Obsolete |
| Category | Industrial Connectors |
| Series | 120234 |
| Description | Brad M23 Power Connector, Front Panel-Mount Receptacle, Straight Female Flange Mount 4xØ 3.20mm, Crimp Contacts, 6 (5+PE) Poles |
| Comments | Crimp Range 0.75-2.50mm² |
| IP Rating | IP67 |
| Product Name | Brad M23 |
| Type | Field Attachable Connector |
| UPC | 883906301552 |

## Electrical

| | |
|---|---|
| Current - Maximum per Contact | 28.0A |
| Voltage - Maximum | 600V |

## Physical

| | |
|---|---|
| Cable Diameter | N/A |
| Coupling Type | N/A |
| Diagnostics / LEDs | No |
| Diagnostics Port | No |
| Gender | Female |
| Keyway | None |
| Material - Connector Body | Nylon |
| Material - Contact | Brass |
| Material - Coupling Nut | N/A |
| Material - Plating Mating | Gold |
| Net Weight | 1.000/g |
| Orientation | Straight |
| Poles | 6 (5+PE) |
| Temperature Range - Operating | -40° to +125°C |
| Wire Size (AWG) | N/A |

Obsolete

Downloaded from Arrow.com.

This document was generated on Sep 23, 2026

Obsolete

Downloaded from Arrow.com.