ME MAX 6,2 DKL TRANS - Housing cover

2200297

https://www.phoenixcontact.com/ae/products/2200297

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 6.3 mm, height: 40.2 mm, depth: 3.6 mm, color: transparent



Your advantages

- Easy, tool-free mounting

Commercial data

Item number	2200297
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	ACH
Product key	ACHABZ
GTIN	4046356555241
Weight per piece (including packing)	0.41 g
Weight per piece (excluding packing)	0.41 g
Customs tariff number	85389099
Country of origin	DE

Downloaded from Arrow.com.

Technical data

Notes

Assembly note	Please observe the application note in the download area.

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 6,2..
Ventilation openings present	no

Dimensions

Width	6.3 mm
Height	40.2 mm
Depth	3.6 mm

Material specifications

Color (Housing cover)	transparent
Material	PC
Flammability rating according to UL 94	V2
CTI according to IEC 60112	250
Insulating material	IIIa
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

PCB data

Type of PCB mount	Latching

Mounting

Mounting type	Latching with lower housing part

Downloaded from Arrow.com.

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/ae/products/2200297

UL Recognized
Approval ID: E240868

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779

UNSPSC

UNSPSC 21.0	31261500

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com

Downloaded from Arrow.com.