



Part Number : [368760001](#)
Product Description : Ditto Hermaphroditic Crimp Terminal, High Copper, Tin Plating, 22-20 AWG
Series Number : 36876
Status : Obsolete
Product Category : Crimp Terminals



Documents and Resources

Specifications

[TS-36876-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	36876
Description	Ditto Hermaphroditic Crimp Terminal, High Copper, Tin Plating, 22-20 AWG
Application	Wire-to-Wire
Product Name	Ditto
UPC	887191582801

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	350V AC/DC

Physical

Durability (mating cycles max)	25
Gender	Hermaphroditic
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.148/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.70mm
Wire Size (AWG)	20, 22
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
-------------	-------------

Ditto Hermaphroditic Crimp Housings	<u>36877</u>
-------------------------------------	--------------

Application Tooling

Global

Description	Part Number
Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals	<u>638131400</u>
Hand Crimp Tool For Ditto Crimp Terminals	<u>638273400</u>
FineAdjust Applicator for Ditto Interconnects Terminals	<u>639030200</u>

This document was generated on May 19, 2026

Obsolete