

© 2021 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	25APR2021	DW	CW
	A1	ECR-21-121080	17NOV2021	DW	CW
	B	ECR-25-237972	16JUN2025	ABS	RB







NOTES:


1. TECHNICAL CHARACTERISTICS:
   INSULATION MATERIAL: PC
   RATED VOLTAGE: 50V AC, 120V DC
   RATED CURRENT: 6.5A
   INSULATION RESISTANCE: >=400MΩ
   RATED IMPULSE VOLTAGE: 0.8KV
   POLLUTION DEGREE: 3
   MATING CYCLES: 500 CYCLES
   WIRE RANGE: 0.08-0.52 mm² (28-20 AWG)
   CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
   (ORDER No. REFER TO DRAWING: T20700X10XX000)


注释：

1. 技术参数：
   绝缘材料： PC
   额定电压： 50V AC, 120V DC
   额定电流： 6.5A
   绝缘电阻： >=400MΩ
   额定脉冲电压： 0.8KV
   污染等级： 3
   插拔次数： 500次
   接线范围： 0.08-0.52 mm² (28-20 AWG)
   接线类型： 冷压接
2. 端子需要单独订购，
   （订货号参考图面： T20700X10XX000）









T2080212201-007	HQ-021-F	HQ-021 FEMALE INSERT HQ-021 母插	
PART NUMBER 产品料号		PART DESCRIPTION 产品描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09MAR2021 DAVID WANG	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	CHK 09MAR2021 GINO YAO APVD 09MAR2021 CHRIS WANG PRODUCT SPEC 108-137560 APPLICATION SPEC 114-137560	NAME HQ-021-F
MATERIAL - -	FINISH - -	WEIGHT -	SIZE A2 · CAGE CODE 00779 · DRAWING NO C⇨T2080212201007 · RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 2:1 · SHEET 1 OF 1 · REV B

Downloaded from Arrow.com.