

SWITCH-BASIC

IXE41

N

**DRAWING
NUMBER**

8	9
7	6


ISSUE

A	CORR
	MBF
5	DEC 52
B	SR10850
	MBF
14	MAR 63
C	C052067
	C JH
21	SEP 82
D	CO
	57328-A
	WJM
15	APR 85
E	C082233
	DLT
11	DEC 85

38

M B F

O-50378



- 1- MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .188 ± .002 CENTERS
- 2- ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3- WEIGHT OF SWITCH ONLY IS .16 OZ MAX.
WEIGHT OF SWITCH WITH WIRE LEADS IS .55 OZ MAX
- 4- COMMON — — — — ORANGE
NORMALLY CLOSED — GREEN
NORMALLY OPEN — — YELLOW

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE 2 TO 1	
OPERATING FORCE — — — — 5-17 OZ		CONTACT ARRANGEMENT S P D T		DO NOT SCALE PRINT	
RELEASE FORCE — — — — 4 OZ MIN		28 VOLTS DC RATING		UNLESS OTHERWISE SPECIFIED	
RELEASE TRAVEL — — — — .004 MIN				DIMENSIONS ARE IN INCHES	
DIFFERENTIAL TRAVEL — — .005 MAX				TOLERANCES ARE:	
OVERTRAVEL — — — — .004 MIN				ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
		INDUCTIVE — — — — SEA LEVEL — — — 4 AMP 50,000 FT — — — 2.5 AMP			
		RESISTIVE — — — — SEA LEVEL — — — 7 AMP 50,000 FT — — — 7 AMP			
		MAXIMUM INRUSH — — — — — 24 AMP		WEIGHT 	