



Part Number : [1200860464](#)

Product Description : Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (90°) to Pigtail, with PNP LED Sensors, 0.34mm² PUR/PVC Cable, 5.0m (16.40') Length

Series Number : 120086

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 4030P1P03M050


Documents and Resources

Drawings

[1200860464_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Triphenyl-phosphate... per D(2025)4165-DC (25 June 2025) SCIP:adc15a28-95fa-416b-99b3-19c9625dbfb2
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (90°) to Pigtail, with PNP LED Sensors, 0.34mm ² PUR/PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	78172553796

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	4.32mm (.170")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	PNP Sensors
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	154.640/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	E152210
Wire Size (AWG)	N/A

This document was generated on Apr 10, 2026