

Protect It! 12-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 2880 Joules, Tel/Modem/Coaxial/Ethernet Protection

MODEL NUMBER: TLP1208SAT



Description

Tripp Lite's TLP1208SAT surge suppressor has 12 outlets, a 8-ft. (2.43 m) cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2880 joules to handle the strongest surges. Built-in RJ11, RJ45, and Type F coax jacks prevent surges from damaging your modem/fax/100Bt/cable/satellite equipment. Coaxial jacks provide digital broadband quality and can handle 2.2GHz bandwidth. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Features

- 12 outlets with integrated child safety covers; black housing
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment on 2 lines simultaneously; 6-ft. (1.83 m) telephone cord included
- Built-in RJ45 jacks prevent surges from damaging your 100Bt equipment; 6-ft. (1.83 m) network cable included
- Built-in gold, Type F coax jacks prevent surges from damaging your cable/satellite equipment; digital broadband quality accommodates 2.2GHz bandwidth; 6-ft. (1.83 m) coax cable included
- Surge suppression rating: 2880 joules
- EMI/RFI noise filtering
- Can accommodate up to 4 transformers without blocking remaining outlets
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Diagnostic LEDs indicate protection present & ground present
- Audible alarm notifies user when the unit is damaged and needs to be replaced
- Keyhole supports for wall mounting

Highlights

- 12 outlets / 8-ft. (2.43 m) cord
- 2880 joule rating
- Coaxial surge protection (digital broadband quality accommodates 2.2GHz bandwidth)
- Ethernet surge protection
- 2-line modem/fax surge protection

Package Includes

- TLP1208SAT
- 6-ft. (1.83 m) telephone cord
- 6-ft. (1.83 m) network cable
- 6-ft. (1.83 m) coax cable
- Instruction manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Lighted power switch
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332175182
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	216000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
Outlet Orientation	Single row of 8, plus a second row of 4 for transformer accommodation
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Audible Alarm	Audible alarm sounds to indicate damage to suppression components
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2880
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330/400/400
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	Yes
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 75mm; Distance between vertical tabs = 41.6mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	Distance between standard outlets = 25.4mm; Distance between transformer outlets = 57mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	31.50 x 6.10 x 22.10
Shipping Dimensions (hwd / in.)	12.40 x 2.40 x 8.70
Shipping Weight (kg)	1.27
Shipping Weight (lbs.)	2.80
Unit Dimensions (hwd / cm)	3.91 x 6.91x x26.16
Unit Dimensions (hwd / in.)	1.54 x 2.72 x 10.30
Unit Weight (kg)	0.92
Unit Weight (lbs.)	2.02
COMMUNICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Network Speed	10/100 Mbps
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>