




NOTES:

1. MATERIALS
HOUSING : UNFILLED NYLON 6/6, RATED UL 94V-2
FOR COLOURS: SEE CHARTS ON SHEETS 2-6.
TERMINALS: 90834-0004 0.38mm IDT PHOSPHOR BRONZE.
0.40/(0.016) THICK REF.
PLATING : 5µm/(200µin) MIN PURE Sn

2. PRODUCT CONFORMS TO SPECIFICATION PS-99020-0037

3. APPLICATION SPECIFICATION AS-99033-0004

4. SEE SUBSEQUENT SHEETS FOR PART NUMBERS SHOWING
THE VARIOUS CODING, KEYING, COLOUR STRIPE AND LATCHING OPTIONS.

5. FOR PACKAGING SPECIFICATION SEE PK-90833-001

Ckt Size	A	B
2	5.00	9.94 +/- 0.04
3	10.00	14.93 +/- 0.05
4	15.00	19.93 +/- 0.05
5	20.00	24.90 +/- 0.08
6	25.00	29.90 +/- 0.08
7	30.00	34.90 +/- 0.08
8	35.00	39.90 +/- 0.08
9	40.00	44.90 +/- 0.08
10	45.00	49.90 +/- 0.08
11	50.00	54.90 +/- 0.08
12	55.00	59.90 +/- 0.08

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS	SCALE	CURRENT REV DESC: UPDATED THE MASTER MODEL P/N				molex			
mm	2:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 654435 DRWN: AKABADI 2020/11/12 CHK'D: SDEVITT 2021/02/26 APPR: SDEVITT 2021/02/26				5MM APPLI-MATE F-INDIRECT CONN ASSY 0.38MM SQ IDT			
ANGULAR TOL	± 0.5°	INITIAL REVISION:				PRODUCT CUSTOMER DRAWING			
4 PLACES	±	DRWN: AKABADI 2016/11/16				DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
3 PLACES	± 0.025	APPR: BRUTTLE 2017/01/11				919540001	PSD	000	E1
2 PLACES	± 0.05								
1 PLACE	± 0.1								
0 PLACES	±								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER			
		A2-SIZE	91954	SEE SHEETS 2-6	GENERAL MARKET	1 OF 6			

13

12

11

10

9

8

7

6

5

4

3

2

1

2 CIRCUIT

MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0001	91778-9021	NATURAL	ALL	ALL	1/2		NONE
91954-0002	91778-9021	NATURAL	1b 2a	ALL	1/2		NONE
91954-0003	91778-9021	NATURAL	1a 2b	01c	1/2		NONE
91954-0004	91778-9021	NATURAL	2a	ALL	1/2		NONE
91954-0005	91778-9021	NATURAL	1a 2b	d20	1/2		NONE
91954-0006	91778-9021	NATURAL	1b 2b	01c	1/2		NONE
91954-0007	91778-9021	NATURAL	1a 2a	01c	1/2		NONE
91954-0008	91778-9021	NATURAL	2b	ALL	1/2		NONE
91954-0009	91778-9021	NATURAL	1a 1b	ALL	1/2		NONE
91954-0010	91778-9021	NATURAL	2b	NONE	1/2		NONE
91954-0011	91778-9021	NATURAL	1a 1b	01c	1/2		NONE
91954-0012	91778-9021	NATURAL	1a	ALL	1/2		NONE
91954-0013	91778-9021	NATURAL	1b 2a	01c	1/2		NONE
91954-0014	91778-9021	NATURAL	ALL	01c	1/2		NONE
91954-0016	91778-9021	NATURAL	1b	ALL	1/2		NONE
91954-0017	91778-9021	NATURAL	1a 2b	NONE	1/2		NONE
91954-0018	91778-9021	NATURAL	2b	d20	1/2		NONE
91954-0019	91778-9021	NATURAL	1a 2a	ALL	1/2		NONE
91954-0020	91778-9021	NATURAL	1b 2a 2b	d20	1/2		NONE
91954-0021	91778-9021	NATURAL	ALL	d20	1/2		NONE
91954-0022	91778-9024	NATURAL	NONE	01c	1/2b		NONE
91954-0024	91778-9021	NATURAL	2a	01c	1/2		NONE
91954-0025	91778-9021	NATURAL	1b 2b	01c	1/2		ORANGE
91954-0026	91778-9021	NATURAL	1a 2b	01c	1/2		BLACK
91954-0027	91778-9021	NATURAL	1b	ALL	1/2		BLUE

2 CIRCUIT

MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0028	91778-9021	NATURAL	1a	ALL	1/2		LIGHT BLUE
91954-0029	91778-9021	NATURAL	1a 2b	d20	1/2		GREEN
91954-0030	91778-9021	NATURAL	2b	NONE	1/2		YELLOW
91954-0031	91778-9021	NATURAL	1a 2b	d20	1/2		BLUE
91954-0032	91778-9021	NATURAL	1b 2a	d20	1/2		NONE
91954-0033	91778-9021	NATURAL	NONE	NONE	1/2		NONE
91954-0034	91778-9024	NATURAL	NONE	NONE	1/2b		NONE
91954-0036	91778-9021	NATURAL	ALL	NONE	1/2		BLACK
91954-0037	91778-9021	NATURAL	2a 2b	01c	1/2		NONE

POSITION KEYS

KEYING, CODING & LATCH IDENTIFICATION
(4 CKT SHOWN IN EXAMPLE)
VIEW IN MATING DIRECTION

= STANDARD LATCH

= SHORT STANDARD LATCH

= SOLID LATCH

1a2b01cD20

CKT 1CKT 2

SOLID LATCH

SHORT STANDARD LATCH

SCALE 3:2

VIEWING DIRECTION

LATCH OPTION 1/2b

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 0.5 °

4 PLACES ±

3 PLACES ± 0.025

2 PLACES ± 0.05

1 PLACE ± 0.1

0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

A2-SIZE

SERIES

91954

CURRENT REV DESC: UPDATED THE MASTER MODEL P/N

EC NO: 654435

DRWN: AKABADI 2020/11/12

CHK'D: SDEVITT 2021/02/26

APPR: SDEVITT 2021/02/26

INITIAL REVISION:

DRWN: AKABADI 2016/11/16

APPR: BRUTTLE 2017/01/11

DOCUMENT NUMBER

919540001

DOC TYPE

PSD

DOC PART

000

REVISION

E1

PRODUCT CUSTOMER DRAWING

MATERIAL NUMBER

SEE SHEETS 2-6

CUSTOMER

GENERAL MARKET

SHEET NUMBER

2 OF 6

DOCUMENT STATUS

P1

RELEASE DATE

2021/02/26

13:43:58

13

12

11

10

9

8

7

6

5

4

3

2


1

Downloaded from

Arrow.com

13		12		11		10		
3 CIRCUIT								
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP	
91954-0101	91778-9031	NATURAL	ALL	ALL	1/2		NONE	
91954-0102	91778-9032	NATURAL	ALL	ALL	2/3		NONE	
91954-0103	91778-9031	NATURAL	1b	01c d20	1/2		NONE	
91954-0104	91778-9031	NATURAL	1a	03c	1/2		NONE	
91954-0105	91778-9031	NATURAL	1a 1b	d30	1/2		NONE	
91954-0106	91778-9031	NATURAL	1b 2a 2b	d30	1/2		NONE	
91954-0107	91778-9032	NATURAL	ALL	d10 d30	2/3		NONE	
91954-0108	91778-9031	NATURAL	1a 3a	01c	1/2		NONE	
91954-0109	91778-9031	NATURAL	1b 3a	01c	1/2		NONE	
91954-0110	91778-9032	NATURAL	2a	02c d30	2/3		NONE	
91954-0111	91778-9031	NATURAL	2b	d20	1/2		NONE	
91954-0112	91778-9031	NATURAL	1b	d20 03c	1/2		NONE	
91954-0113	91778-9032	NATURAL	1a 1b 2a 3a	01c 02c d30	2/3		NONE	
91954-0114	91778-9032	NATURAL	1a 2a	d30	2/3		NONE	
91954-0115	91778-9032	NATURAL	2a	d10 d30	2/3		NONE	
91954-0116	91778-9031	NATURAL	3b	01c d30	1/2		NONE	
91954-0117	91778-9032	NATURAL	2b 3b	d10 02c	2/3		NONE	
91954-0118	91778-9032	NATURAL	2a	d10 02c d30	2/3		NONE	
91954-0119	91778-9031	NATURAL	1a	01c d20 03c	1/2		NONE	
91954-0120	91778-9031	NATURAL	1b 2a	01c d20	1/2		NONE	
91954-0122	91778-9031	NATURAL	1a 1b 2b	01c	1/2		NONE	
91954-0123	91778-9031	NATURAL	NONE	01c d30	1/2		NONE	
91954-0124	91778-9037	NATURAL	2a 3b	NONE	2/3b		NONE	
DOCUMENT STATUS P1 RELEASE DATE 2021/02/26 13:43:58								

4 CIRCUIT							
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0201	91778-9041	NATURAL	ALL	ALL	1/2 3/4		NONE
91954-0202	91778-9041	NATURAL	1b	03c d40	1/2 3/4		NONE
91954-0203	91778-9041	NATURAL	ALL	d20 03c	1/2 3/4		NONE
91954-0204	91778-9041	NATURAL	1b	d20 03c	1/2 3/4		NONE
91954-0205	91778-9041	NATURAL	1a 4b	d40	1/2 3/4		NONE
91954-0206	91778-9041	NATURAL	1a 3a 3b	01c d20 d40	1/2 3/4		NONE
91954-0207	91778-9041	NATURAL	1b 2a 3a 4b	01c d40	1/2 3/4		NONE
91954-0208	91778-9041	NATURAL	1a 4b	01c	1/2 3/4		NONE
91954-0209	91778-9042	NATURAL	3b	d30	2/3		NONE
91954-0210	91778-9041	NATURAL	1a 1b 3a 3b	01c 03c	1/2 3/4		NONE
91954-0211	91778-9041	NATURAL	1a 2a 4a	01c 03c d40	1/2 3/4		NONE
91954-0212	91778-9041	NATURAL	1a 1b 3a 3b	ALL	1/2 3/4		NONE
91954-0213	91778-9041	NATURAL	3b 4a	01c d20 03c	1/2 3/4		NONE
91954-0214	91778-9041	NATURAL	ALL	01c	1/2 3/4		NONE



LATCH OPTION 1/2b

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 0.5°

4 PLACES ±

3 PLACES ± 0.025

2 PLACES ± 0.05

1 PLACE ± 0.1

0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

A2-SIZE

SERIES

91954

CURRENT REV DESC: UPDATED THE MASTER MODEL P/N

EC NO: 654435

DRWN: AKABADI 2020/11/12

CHK'D: SDEVITT 2021/02/26

APPR: SDEVITT 2021/02/26

INITIAL REVISION:

DRWN: AKABADI 2016/11/16

APPR: BRUTTLE 2017/01/11

DOCUMENT NUMBER

919540001

DOC TYPE

PSD

DOC PART

000

REVISION

E1

PRODUCT CUSTOMER DRAWING

5MM APPLI-MATE F-INDIRECT CONN ASSY 0.38MM SQ IDT

MATERIAL NUMBER


SEE SHEETS 2-6

CUSTOMER

GENERAL MARKET



SHEET NUMBER

3 OF 6



KEYING, CODING & LATCH IDENTIFICATION (4 CKT SHOWN IN EXAMPLE) VIEW IN MATING DIRECTION








5 CIRCUIT							
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0301	91778-9053	NATURAL	1a 3a	01c d30	1/2 4/5		NONE
91954-0302	91778-9051	NATURAL	1a 5b	01c d20 03c d50	1/2 3/4		NONE
91954-0303	91778-9052	NATURAL	2a	01c d50	2/3 4/5		NONE
91954-0304	91778-9052	NATURAL	ALL	01c d50	2/3 4/5		NONE
91954-0305	91778-9052	NATURAL	ALL	ALL	2/3 4/5		NONE
91954-0306	91778-9051	NATURAL	ALL	ALL	1/2 3/4		NONE
91954-0307	91778-9053	NATURAL	ALL	ALL	1/2 4/5		NONE
91954-0308	91778-9051	NATURAL	2a 4b	01c d20 d40	1/2 3/4		NONE
91954-0309	91778-9053	NATURAL	1a 3a	01c d30 d50	1/2 4/5		NONE
91954-0310	91778-9051	NATURAL	NONE	01c d40	1/2 3/4		NONE
91954-0313	91778-9054	NATURAL	1a 2b 3b 4b 5b	d10 02c 04c d50	4/5		NONE
91954-0314	91778-9054	NATURAL	5b	01c d20 03c d50	4/5		NONE












KEYING, CODING & LATCH IDENTIFICATION
(4 CKT SHOWN IN EXAMPLE)
VIEW IN MATING DIRECTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS mm		SCALE 1:1		CURRENT REV DESC: UPDATED THE MASTER MODEL P/N			molex		
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL		± 0.5 °		EC NO: 654435			5MM APPLI-MATE F-INDIRECT CONN ASSY 0.38MM SQ IDT		
4 PLACES		±		DRWN: AKABADI 2020/11/12					
3 PLACES		± 0.025		CHK'D: SDEVITT 2021/02/26					
2 PLACES		± 0.05		APPR: SDEVITT 2021/02/26			PRODUCT CUSTOMER DRAWING		
1 PLACE		± 0.1		INITIAL REVISION:					
0 PLACES		±		DRWN: AKABADI 2016/11/16			DOCUMENT NUMBER		
				APPR: BRUTTLE 2017/01/11			919540001		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING A2-SIZE		SERIES 91954		MATERIAL NUMBER SEE SHEETS 2-6	
						CUSTOMER GENERAL MARKET		SHEET NUMBER 4 OF 6	






6 CIRCUIT


MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0401	91778-9061	NATURAL	ALL	ALL	2/3 4/5		NONE
91954-0402	91778-9062	NATURAL	1b	03c d60	1/2 5/6		NONE
91954-0403	91778-9062	NATURAL	ALL	ALL	1/2 5/6		NONE
91954-0404	91778-9062	NATURAL	5b	01c d40	1/2 5/6		NONE
91954-0405	91778-9062	NATURAL	1b 6a	d30	1/2 5/6		NONE
91954-0406	91778-9062	NATURAL	2b 6b	d40	1/2 5/6		NONE
91954-0407	91778-9063	NATURAL	5b	02c 06c	3/4		NONE
91954-0408	91778-9064	NATURAL	1b 3a 4b 5a 5b 6b	01c d60	2/3		NONE
91954-0409	91778-9063	NATURAL	1b 2a 5b 6b	d50 06c	3/4		NONE

7 CIRCUIT

MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0501	91778-9071	NATURAL	2b	d20 07c	1/2 5/6		NONE
91954-0502	91778-9071	NATURAL	ALL	ALL	1/2 5/6		NONE
91954-0503	91778-9071	NATURAL	NONE	d20	1/2 5/6		NONE
91954-0504	91778-9072	NATURAL	ALL	ALL	2/3 6/7		NONE
91954-0505	91778-9072	NATURAL	ALL	02c d50	2/3 6/7		NONE
91954-0506	91778-9073	NATURAL	NONE	d20 03c 07c	5/6		NONE
91954-0507	91778-9074	NATURAL	1a 6b	03c 07c	4/5		NONE
91954-0508	91778-9071	NATURAL	NONE	04c 05c	1/2 5/6		NONE
91954-0509	91778-9071	NATURAL	NONE	04c 07c	1/2 5/6		NONE

8 CIRCUIT

MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0601	91778-9081	NATURAL	ALL	ALL	3/4 5/6		NONE
91954-0602	91778-9081	NATURAL	1b 3a 3b 5a 5b 7a 8a	01c d20 03c 05c 07c	3/4 5/6		NONE
91954-0603	91778-9082	NATURAL	ALL	ALL	1/2 7/8		NONE
91954-0604	91778-9082	NATURAL	ALL	03c d60	1/2 7/8		NONE
91954-0605	91778-9082	NATURAL	2b 8a	03c d60	1/2 7/8		NONE
91954-0606	91778-9083	NATURAL	8b	02c d30 07c	2/3 7/8		NONE
91954-0607	91778-9084	NATURAL	2b 8a	03c d60	1/2		NONE
91954-0608	91778-9085	NATURAL	8b	02c d30	2/3		NONE



KEYING, CODING & LATCH IDENTIFICATION
(4 CKT SHOWN IN EXAMPLE)
VIEW IN MATING DIRECTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED THE MASTER MODEL P/N				molex							
mm		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 654435				5MM APPLI-MATE F-INDIRECT CONN ASSY 0.38MM SQ IDT							
ANGULAR TOL ± 0.5 °															
4 PLACES		±		DRWN: AKABADI 2020/11/12				PRODUCT CUSTOMER DRAWING							
3 PLACES		± 0.025		CHK'D: SDEVITT 2021/02/26											
2 PLACES		± 0.05		APPR: SDEVITT 2021/02/26				DOCUMENT NUMBER 919540001							
INITIAL REVISION:				DOC TYPE								DOC PART		REVISION	
1 PLACE		± 0.1		DRWN: AKABADI 2016/11/16				PSD		000		E1			
0 PLACES		±		APPR: BRUTTLE 2017/01/11											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
								A2-SIZE		91954		SEE SHEETS 2-6		GENERAL MARKET	


DOCUMENT STATUS	P1	RELEASE DATE	2021/02/26	13:43:58
-----------------	----	--------------	------------	----------

9 CIRCUIT							
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0701	91778-9091	NATURAL	ALL	ALL	3/4 6/7		NONE
91954-0702	91778-9091	NATURAL	1b 2a 3a 5a 6a 7b 8b	01c 03c d70 08c d90	3/4 6/7		NONE
91954-0703	91778-9093	NATURAL	2b 5a	d80	2/3 7/8		NONE
91954-0704	91778-9092	NATURAL	1b	03c	5/6		NONE
91954-0705	91778-9094	NATURAL	2b 3b 4a 5a 6b	d10 02c 04c 08c d90	2/3 4/5 6/7 8/9		NONE
91954-0706	91778-9095	NATURAL	1b 2a 4b 5a 8b 9b	01c d20 d70 08c	1/2 4/5 6/7 8/9		NONE

10 CIRCUIT							
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0801	91778-9101	NATURAL	ALL	ALL	3/4 7/8		NONE
91954-0802	91778-9101	NATURAL	1a 3b 7b 8a	01c d20 d40 05c d100	3/4 7/8		NONE
91954-0803	91778-9102	NATURAL	ALL	ALL	4/5 7/8		NONE
91954-0804	91778-9103	NATURAL	ALL	ALL	4/5 6/7		NONE
91954-0805	91778-9102	NATURAL	1a 10b	07c	4/5 7/8		NONE
91954-0806	91778-9103	NATURAL	1b 9a	06c	4/5 6/7		NONE
91954-0807	91778-9104	NATURAL	1b	03c	5/6		NONE
91954-0808	91778-9104	NATURAL	4b 6b 8a 8b	d100	5/6		NONE
91954-0809	91778-9105	NATURAL	4b 6b 8a 8b	06c d100	NONE		NONE

11 CIRCUIT							
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-0901	91778-9111	NATURAL	ALL	ALL	3/4 8/9		NONE
91954-0902	91778-9111	NATURAL	1a 2b 3b 4a 4b 5a 7a 8a 9a 10a 11a	01c d40 05c 08c 10c	3/4 8/9		NONE

12 CIRCUIT							
MOLEX PART NO.	HOUSING NO.	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP
91954-1001	91778-9121	NATURAL	ALL	ALL	3/4 9/10		NONE
91954-1002	91778-9121	NATURAL	1a 2a 4a 4b 5a 6b 8a 11a	01c 03c 05c 07c d80 d100 11c	3/4 9/10		NONE



KEYING, CODING & LATCH IDENTIFICATION
(4 CKT SHOWN IN EXAMPLE)
VIEW IN MATING DIRECTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	CURRENT REV DESC: UPDATED THE MASTER MODEL P/N	
mm	1:1		
GENERAL TOLERANCES (UNLESS SPECIFIED)			
ANGULAR TOL	± 0.5 °	EC NO: 654435	
4 PLACES	±	DRWN: AKABADI 2020/11/12	
3 PLACES	± 0.025	CHK'D: SDEVITT 2021/02/26	
2 PLACES	± 0.05	APPR: SDEVITT 2021/02/26	
1 PLACE	± 0.1	INITIAL REVISION:	
0 PLACES	±	DRWN: AKABADI 2016/11/16	
		APPR: BRUTTLE 2017/01/11	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING
			A2-SIZE
		SERIES	91954

mo

lex

5MM APPLI-MATE
F-INDIRECT CONN ASSY 0.38MM SQ IDT

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
919540001	PSD	000	E1
MATERIAL NUMBER	CUSTOMER		SHEET NUMBER
SEE SHEETS 2-6	GENERAL MARKET		6 OF 6

DOCUMENT STATUS	P1	RELEASE DATE	2021/02/26	13:43:58
-----------------	----	--------------	------------	----------

13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---