


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

- DO-IT-YOURSELF (DIY) 4 mm IN-LINE JACK, SOLDER ATTACHMENT.
- SPECIFICATIONS:  
INSULATOR BODY: POLYAMIDE (NYLON)  
JACK BODY: BRASS, NICKEL PLATED
- RATING:  
VOLTAGE: 1,200V AC/DC  
CURRENT: 36A MAX.  
TEMPERATURE: -20°C TO +80°C.
- MAXIMUM WIRE SIZES:  
CONDUCTOR: Ø2.3 (.090) (12AWG)  
STRIP LENGTH: 6.4 (.25)

**PART NUMBER**

**CT2213-#**

COLOR: 0 - BLACK  
2 - RED  
4 - YELLOW  
5 - GREEN  
6 - BLUE  
9 - WHITE



# REVISIONS

REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/11/99	
A	UPDATED TO METRIC FORMAT	3/9/19	

**METRIC**


UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN MILLIMETERS  
TOLERANCES ARE:  
DECIMALS ANGLE  
.X ± 0.8 ± 2°  
.XX ± 0.25  
DO NOT SCALE DRAWING

CONTRACT NO.

**Cal Test Electronics**

22820 Savi Ranch Parkway  
Yorba Linda, CA 92887-4610

THIRD ANGLE PROJECTION



MATERIAL

FINISH

APPROVALS

DATE

DRAWN WDH

7/11/99

CHECKED

ENGR.

DESIGN ACTIVITY

TITLE

**DIY 4 mm JACK, SOLDER**

SIZE  
**A**

CAGE CODE  
**43F45**

DWG. NO.

**P221300**

REV.  
**A**

SCALE 1:1

SHEET 1 OF 1