Part Number : 1200905078
Product Description : Nano-Change (M8) Receptacle, 4 Poles, A-Coded, M8 x 1.0 Mounting Threads, Male (Straight) to Leads, Back Panel Mount, 0.20m (7.87") Length
Series Number : 120090
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 4R4F46E02C200



Documents and Resources

Drawings

1200905078_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate; Lead monoxide per D(2025)4165-DC (25 June 2025) SCIP:8a29228f-9545-48db-976f-1009b55e213d
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	120090
Description	Nano-Change (M8) Receptacle, 4 Poles, A-Coded, M8 x 1.0 Mounting Threads, Male (Straight) to Leads, Back Panel Mount, 0.20m (7.87") Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	883906784553

Agency

UL	E152210

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	A-Coded

Downloaded from Arrow.com.

Length	0.20m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 1.0
Net Weight	79.140/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 1569
Wire Size (AWG)	24

Downloaded from Arrow.com.