






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




INDICATOR			
SWITCH	LED		
	RED	GREEN	BLUE
OFF	ON	CUSTOMER DEFINED	
ON	OFF		




APPLICABLE FOR TE P/N:
2342834-2
2342834-4
2342834-6

PRELIMINARY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GANESH C M 29SEP2018	 TE Connectivity Ltd.					
		CHK ALEXANDER SHARPE 29SEP2018						
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD ALEXANDER SHARPE 29SEP2018	NAME					
	0 PLC ± -	PRODUCT SPEC	SWITCH,AV,CAPACITIVE,19mm,FL BTN, ILLUM RING,LED,LEADED W/ 1x6 REC					
	1 PLC ± 0.4[.016]	—						
	2 PLC ± 0.25[.010]	APPLICATION SPEC						
	3 PLC ± -	—						
4 PLC ± -	—	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL	FINISH	WEIGHT	A3	00779	C-2342834	—		
CUSTOMER DRAWING			SCALE	NTS	SHEET	2 of 3	REV	3

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

- NOTES:
1. SPECIFICATIONS:
- 1. OPERATING LIFE: 50 MILLION CYCLES MIN.
 - 2. ACTUATION FORCE: TOUCH, ZERO FORCE
 - 3. RATING: 5-24 VDC@1A MAX.
 - 4. CONTACT RESISTANCE: 1Ω MAX.
 - 5. CURRENT DRAW WITHOUT ILLUMINATION: 2mA MAXIMUM
 - 6. CURRENT DRAW WITH ILLUMINATION: 10mA MAXIMUM
 - 7. OUTPUT MODE: NPN TRANSISTOR
 - 8. OPERATING TEMPERATURE: -20° TO 65°C [-4° TO 149°F]
 - 9. STORAGE TEMPERATURE: -40° TO 85°C [-40° TO 185°F]
 - 10. INGRESS PROTECTION: IP68, PANEL SIDE
 - 11. MOUNTING TORQUE: 2.5Nm MAXIMUM
2. MATERIAL:
- 1. SEALING: SILICONE, EPOXY
 - 2. O-RING: SILICONE
 - 3. HEX NUT: NICKEL PLATED BRASS
 - 4. WIRE: UL3385, UL10368 OR EQUIVALENT
 - 5. BUSHING: SEE TABLE
 - 6. CAP: SEE TABLE
3. PACKAGING:
- SWITCH ASSEMBLIES ARE INDIVIDUALLY BUNDLED WITH ESD PROTECTION.
HARDWARE IS NOT ASSEMBLED TO THE SWITCH.
4. COMPLIANCE:
- THE CURRENT STATEMENT OF COMPLIANCE IS AVAILABLE AT TE.COM.
5. HARDWARE IS SHIPPED UNASSEMBLED.

PC; STAINLESS STEEL	STAINLESS STEEL 316	RGB	MOMENTARY	AVC19MS16FE0DT5A04	2342834-9		
PC; STAINLESS STEEL	STAINLESS STEEL 304	RGB	MOMENTARY	AVC19MS04FE0DT5A04	2342834-8		
PC; ALUMINUM	ALUMINUM	RGB	MOMENTARY	AVC19MAIOFE0DT5A04	2342834-7		
PC; STAINLESS STEEL	STAINLESS STEEL 316	RED LOCK	LOCKING	AVC19LS16FE03T5A04	2342834-6		
PC; STAINLESS STEEL	STAINLESS STEEL 316	RGB	LOCKING	AVC19LS16FE0DT5A04	2342834-5		
PC; STAINLESS STEEL	STAINLESS STEEL 304	RED LOCK	LOCKING	AVC19LS04FE03T5A04	2342834-4		
PC; STAINLESS STEEL	STAINLESS STEEL 304	RGB	LOCKING	AVC19LS04FE0DT5A04	2342834-3		
PC; ALUMINUM	ALUMINUM	RED LOCK	LOCKING	AVC19LAIOFE03T5A04	2342834-2		
PC; ALUMINUM	ALUMINUM	RGB	LOCKING	AVC19LAIOFE0DT5A04	2342834-1		
CAP MATERIAL	BUSHING MATERIAL	LED COLOR	CONTACT CONFIGURATION	TE SMART PART NUMBER	PART NUMBER		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29SEP2018 GANESH C M	 TE Connectivity Ltd.				
		CHK 29SEP2018 ALEXANDER SHARPE					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.4[.016] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± - ± -	APVD 29SEP2018 ALEXANDER SHARPE	NAME SWITCH,AV,CAPACITIVE,19mm,FL BTN, ILLUM RING,LED,LEADED W/ 1x6 REC				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		MATERIAL —				FINISH —	WEIGHT
		CUSTOMER DRAWING			SCALE NTS	SHEET 3 OF 3	REV 3

PRELIMINARY