




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:


1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE MILLIMETERS (IN).
3. PARTS SUPPLIED:
 - (1) - BLANKING PANEL WITH BRUSH SEAL
 - (4) - M6 X1X12MM PHILLIPS HEAD SCREW
 - (4) - M6 X1MM CAGE NUT
 - (4) - #12-24 X 1/2" SCREW
4. COLOR:BLACK
5. THE BRUSHES ARE UL94-V0 RATED

PANDUIT P/N	WEIGHT
BR2B	0.5 Kg/EACH 1.1 LBS/EACH



SCALE 1:5
BACK SIDE VIEW

TITLE											
19" 2 RU Brush Seal Blank Panel with Front to Back Cable Passthrough											
CUSTOMER DRAWING											
ITEM REVISION NAME						PANDUIT					
00132EAB/01											
DATASET FILE NAME						MATERIAL:					
00132EAB_DC/01A											
						N/A					
THIRD ANGLE PROJECTION						DRAWING NUMBER:					
00132EAB - DC											
DRAWN BY		DATE		CHK		SCALE		SIZE			
CHN-LLK		2018 Jan 30		MWH		1:4		SHT 1 OF 1			
								A			



THIRD ANGLE
PROJECTION

010100DA/16