



Part Number : [2039300406](#)

Product Description : Impulse 90 Ohm 3-Pair
Vertical Header, 2.00mm Pitch, Unguided, 14 Columns,
42 Differential Pair

Series Number : 203930

Status : Active

Product Category : Backplane Connectors



Documents and Resources

Drawings

[2039300406_sd.pdf](#)

[3006409035-000.pdf](#)

[2039300000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[3006409035-000.zip](#)

Specifications

[1735109996-AS-000.pdf](#)

[1735109997-AS-000.pdf](#)

[1735109998-AS-000.pdf](#)

[1735109999-AS-000.pdf](#)

[1735109000-PS-000.pdf](#)

Tooling Specifications

[3006409035-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	203930
Description	Impulse 90 Ohm 3-Pair Vertical Header, 2.00mm Pitch, Unguided, 14 Columns, 42 Differential Pair
Application	Backplane
Component Type	PCB Header
Product Name	Impulse
UPC	196823147838

Electrical

Current - Maximum per Contact	0.75A
-------------------------------	-------

Data Rate	112 Gbps (PAM-4)
Impedance	90Ω
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	150V AC (RMS)/DC

Physical

Circuits (Loaded)	84
Circuits (maximum)	84
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	No
Material - Metal	High Performance Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.851/g
Number of Columns	14
Number of Pairs	3
Number of Rows	6
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.30mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762μm
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impulse 90 Ohm 3-Pair Orthogonal Daughtercard, 2.00mm Pitch, Unguided, 14 Columns, 42 Differential Pair	<u>2081001054</u>

This document was generated on May 13, 2026