

Features

- Halogen Free. "Green" Device (Note 1)
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings @ 25°C Unless Otherwise Specified

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Maximum Thermal Resistance: 833°C/W Junction to Ambient

Parameter	Symbol	Rating	Unit
Collector-Base Voltage BC856A-BC856B BC857A-BC857C BC858A-BC858C	V_{CBO}	-80 -50 -30	V
Collector-Emitter Voltage BC856A-BC856B BC857A-BC857C BC858A-BC858C	V_{CEO}	-65 -45 -30	V
Emitter-Base Voltage	V_{EBO}	-5	V
Collector Current	I_C	-100	mA
Collector Power Dissipation	P_C	150	mW


Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Marking:

BC856A:3A; BC856B:3B;
BC857A:3E; BC857B:3F; BC857C:3G;
BC858A:3J; BC858B:3K; BC858C:3L;

PNP Plastic-Encapsulate Transistors


DFN1006-3



DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.018	0.022	0.45	0.55	
A1	0.000	0.002	0.00	0.05	
b	0.018	0.022	0.45	0.55	
b1	0.004	0.008	0.10	0.20	
c	0.005	0.007	0.12	0.18	
D	0.037	0.042	0.95	1.075	
E	0.022	0.026	0.55	0.675	
E1	0.006	0.010	0.15	0.25	
e	0.026		0.65		TYP.
L	0.008	0.012	0.20	0.30	
L1	0.0002		0.05		TYP.

Suggested Solder Pad Layout



Electrical Characteristics @ $T_A=25^{\circ}\text{C}$ Unless Otherwise Specified

Parameter	Symbol	Min	Typ	Max	Units	Conditions
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$				V	$I_C=-10\mu\text{A}, I_E=0$
BC856A-BC856B		-80				
BC857A-BC857C		-50				
BC858A-BC858C		-30				
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$				V	$I_C=-10\text{mA}, I_B=0$
BC856A-BC856B		-65				
BC857A-BC857C		-45				
BC848A-BC848C		-30				
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$				V	$I_E=-1\mu\text{A}, I_C=0$
BC856A-BC856B		-5				
BC857A-BC857C		-5				
BC858A-BC858C		-5				
Collector Cut-off Current	I_{CBO}			-15	nA	$V_{CB}=-30\text{V}, I_E=0$
Emitter Cutoff Current	I_{EBO}			-100	nA	$V_{EB}=-5\text{V}, I_C=0$
Emitter Cutoff Current	I_{CEO}			-1	mA	$V_{CE}=-30\text{V}, I_B=0$
DC Current Gain	h_{FE}					$V_{CE}=-5\text{V}, I_C=-2\text{mA}$
BC856A/BC857A/BC858A		110		220		
BC856B/BC857B/BC858B		200		450		
BC857C/BC858C		420		800		
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$			-0.3	V	$I_C=-10\text{mA}, I_B=-0.5\text{mA}$
				-0.65		$I_C=-100\text{mA}, I_B=-5\text{mA}$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$		-0.7		V	$I_C=-10\text{mA}, I_B=-0.5\text{mA}$
			-0.85			$I_C=-100\text{mA}, I_B=-5\text{mA}$
Base-Emitter On Voltage	$V_{BE(on)}$	-0.6	-0.65	-0.75	V	$V_{CE}=-5\text{V}, I_C=-2\text{mA}$
				-0.82		$V_{CE}=-5\text{V}, I_C=-10\text{mA}$
Transition Frequency	f_T	100			MHz	$V_{CE}=-5\text{V}, I_C=-10\text{mA}, f=100\text{MHz}$

Curve Characteristics

Fig. 1 - Static Characteristics




Fig. 2 - DC Current Gain Characteristics




Fig. 3 - Collector-Emitter Saturation Voltage Characteristics




Fig. 4 - Base-Emitter Saturation Voltage Characteristics




Fig. 5 - Base-Emitter Voltage Characteristics





Fig. 6 - Collector Power Derating Curve



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel: 10Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp**. products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.