

S5295B/G/J

PRV : 100 - 600 Volts

Io : 0.5 Ampere

FEATURES :


- * High current capability
- * High surge current capability
- * High reliability
- * Low reverse current
- * Low forward voltage drop
- * Fast switching for high efficiency
- * **Pb / RoHS Free**

MECHANICAL DATA :

- * Case : DO-41 Molded plastic
- * Epoxy : UL94V-O rate flame retardant
- * Lead : Axial lead solderable per MIL-STD-202, Method 208 guaranteed
- * Polarity : Color band denotes cathode end
- * Mounting position : Any
- * Weight : 0.339 gram

FAST RECOVERY RECTIFIERS

DO - 41



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified.
Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

RATING	SYMBOL	S5295B	S5295G	S5295J	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	100	400	600	V
Maximum Reverse Voltage (DC)	V_R	75	300	500	V
Maximum Average Forward Current	$I_{F(AV)}$	0.5			A
Maximum Peak One Cycle Surge Forward Current (50 Hz, Non-Repetitive)	I_{FSM}	30			A
Maximum Peak Forward Voltage at $I_F = 1.0$ A	V_F	1.5			V
Maximum Repetitive Peak Reverse Current at V_{RRM}	I_R	10			μA
Maximum Reverse Recovery Time (Note 1)	T_{rr}	1.5			μs
Junction Temperature Range	T_J	- 40 to + 125			°C
Storage Temperature Range	T_{STG}	- 40 to + 125			°C

Notes :

(1) Reverse Recovery Test Condition : $I_F = 20$ mA, $I_R = 1$ mA

RATING AND CHARACTERISTIC CURVES (S5295B/G/J)

FIG.1 - REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM




FIG.2 - DERATING CURVE FOR OUTPUT RECTIFIED CURRENT




FIG.3 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.4 - TYPICAL FORWARD CHARACTERISTICS




FIG.5 - TYPICAL REVERSE CHARACTERISTICS

