Part Number : 2206030102
Product Description : Mini-Fit Max Right-Angle Header, Dual Row, Through Hole, 2 Circuits, Matte Tin (Sn) Plating, Black, Glow-Wire Capable, Tray
Series Number : 220603
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2206030102_sd.pdf

2206030001-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

2125150001-AS-000.pdf

2125150000-PS-000.pdf

2125150000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	220603
Description	Mini-Fit Max Right-Angle Header, Dual Row, Through Hole, 2 Circuits, Matte Tin (Sn) Plating, Black, Glow-Wire Capable, Tray
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Mini-Fit Max
UPC	198282794271

Agency

UL	E29179

Electrical

Current - Maximum per Contact	20.5A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2

Downloaded from Arrow.com.

Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	1.050/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm-2.40mm
PC Tail Length	3.80mm
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Plating min - Mating	1.520µm
Plating min - Termination	1.520µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	None
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Downloaded from Arrow.com.

Description	Part Number
Mini-Fit Max Dual Row Receptacle Housings	212514

Downloaded from Arrow.com.