


39501000440 - 395 Series



Series: 395

 [Fuse 395 Datasheet](#)

- Features:**
- Reduced PCB space requirements
 - Direct solderable or plug-in versions
 - Internationally approved
 - Low internal resistance
 - Shocksafe casing
 - Vibration resistant
 - Halogen free
 - CCCe for China import

Click on part number below for individual TC curve files.

Questions? [Contact Littelfuse Support](#)

 Check Stock

 Order Samples





Feedback

Electrical Characteristics		Technical Resources	Environmental Info
Property (Mouseover for details)	Value		
Ampere Rating (A)	0.1		
Nominal Melting I ² T (A ² sec)	0.0013		
Interrupting Rating	100A@125VAC		
Min Operating Temp °C	-40		
Max Operating Temp (°C)	85		
Moisture Sensitivity Level	MIL-STD-202 Method 106		
Nominal Power Dissipation (W)	110		
Nominal Voltage Drop (mV)	1100		
Nominal Cold Resistance (Ohms)	7.491		
Opening	Fast-Acting (F)		
Package Size	TE5 (8.5x8mm)		
VAC (V)	125		

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).





- About Littelfuse
- About Littelfuse

Conflict Free Statement

History

Investor Relations

Legal

Press Room

Privacy Statement

Supply Chain Transparency

Website Feedback

- Explore Littelfuse
- Capabilities Brochures

Careers

Check Distributor Stock

Competitor Cross Reference

Industries

Order Samples

Products

Services

- Technical Resources
- Application Designs

Education

FAQs

iDesign™

Littelfuse University

Product Catalogs

Quality Documents

Technical Documents