







P1	COLOR
1	WHITE
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN



A, B, C, D, E



F, G

Note:

- Material: Housing-polycarbonate, clear
Terminal-0.36[.014] thick phosphor bronze.
Thick gold in localized gold plate.
Area, Gold Flash over the remainder.
Over 2.54mm[.000100] thick nickel underplate.

Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length
AT-S-26-8/8/B-5-OE	A	1,525±20(5ft)	Black	1,525-1,535mm
AT-S-26-8/8/B-7-OE	B	2,135±30(7ft)	Black	2,135-2,145mm
AT-S-26-8/8/B-10-OE	C	3,050±60(10ft)	Black	3,050-3,060mm
AT-S-26-8/8/B-12-OE	D	3,660±60(12ft)	Black	3,660-3,670mm
AT-S-26-8/8/B-14-OE	E	4,270±60(14ft)	Black	4,270-4,280mm
AT-S-26-8/8/B-25-OE	F	7,625±100(25ft)	Black	7,625-7,635mm
AT-S-26-8/8/B-50-OE	G	15,250±150(50ft)	Black	15,250-15,260mm

Unit: mm

RoHS Compliant

Scale	Free
TOLERANCE	
X.	±X
X.X	±X
X.XX	±X
DIM	TOL
X.°	±X°
X.X°	±X°
Angle	TOL

Id.	Modification	Date	Name

	Date	Name
Drawn	01.07.13	Wilson
Approved	01.07.13	Groll

ASSMANN WSW components
1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@assmann.us

Title
Modular cable - Straight/Open
8P8C 50µ", 26AWG, Black, 5-50 feet

ASSMANN WSW-No.
AT-S-26-8/8/B-xx-OE

Drawing-No.

rev00

Replace

Sheet 1/1

Downloaded from Arrow.com.