
Part Number : 5013951000
Product Description : 3.30mm Pitch Crimp Terminal, Female, 20-18 AWG, Reel
Series Number : 501395
Status : Obsolete
Product Category : Crimp Terminals



Documents and Resources

Drawings

5013951000_sd.pdf

Tooling Specifications

574113700ATS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	501395
Description	3.30mm Pitch Crimp Terminal, Female, 20-18 AWG, Reel
Product Name	N/A
UPC	822348810550

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	169.000/mg
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.75-2.60mm
Wire Size (AWG)	18, 20
Wire Size mm^2	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
3.30mm Pitch Wire-to-Wire Inertia Lock Single Row Plug Housings	501329
3.30mm Pitch Male Crimp Terminals	56265

Use with Part(s)

Description	Part Number

Obsolete

Downloaded from Arrow.com.

3.30mm Pitch Wire-to-Wire Inertia Lock Single Row Receptacle Housings	501328
3.30mm Pitch Wire-to-Board Receptacle Housings	51284
3.30mm Pitch Receptacle Housings	51347

Application Tooling

This document was generated on Oct 05, 2026

Obsolete

Downloaded from Arrow.com.