


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



- NOTE:
- MATERIAL, HOUSING: HIGH TEMP THERMAL PLASTIC, UL94-V0
TERMINAL: COPPER ALLOY
 - FINISH: TERMINAL: GOLD AT CONTACT, G/F OVER $1\mu\text{M}(40\text{u"})$ MIN NI OVER ALL
 - SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
 - THE HSG. WILL WITHSTAND EXPOSURE TO 260C PEAK TEMP. FOR 10 SEC. IN A WAVE SOLDER APPLICATION.
 - MATING SIDE LENGTH: 2.5MM MIN.
 - PRODUCT NUMBERING:
200218 1 1 - XXX XX X X LF

LEAD FREE
PLATING:
1: G/F ALL OVER
4: $0.25\mu\text{M}(10\text{u"})$ GOLD AT CONTACT
8: $0.76\mu\text{M}(30\text{u"})$ GOLD AT CONTACT
PACKING
T: TUBE
PIN COUNT
04, 06, 08, ..., 98, A0
(EVERY EVEN PIN)
STACK HEIGHT "K"
EXAMPLE: 045=4.5MM
IN 0.5MM INCREMENT



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.38	projection 	title 1.27X1.27MM BTB STACK HD		
A	T10-0065	S.LIN	10'-5-20		.XX ± 0.25		VT, TH		
					.XXX ± 0.15		product family 585		
				angles	0° $\pm 2'$	MM ← → scale NA	code size dwg no		
				dr	STERLING LIN		10'-5-20	585	
				engr	STERLING LIN		10'-5-20	TWN	
				chr	STERLING LIN		10'-5-20	sheet	
				appd	GARY HSIEH		10'-5-20	1 of	
sheet index	revision sheet	A	1				20021811		