


# UC-WMTBA (24X5) BU - Cable marker



0820552

<https://www.phoenixcontact.com/us/products/0820552>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Sheet, blue, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: Assembly with cable ties, cable diameter: > 4 mm, Number of individual labels: 12, text field height: 5 mm, text field width: 24 mm

## Your advantages

- The UC-WMTBA ... UniCard labeling range includes markers that can be secured using standard cable binders
- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing systems
- For large-surface marking of conductors and cables >4 mm in diameter
- Thanks to their angular shape the markers fit perfectly onto cables
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0820552       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG10          |
| Product key                          | BG2317        |
| GTIN                                 | 4046356290678 |
| Weight per piece (including packing) | 9.421 g       |
| Weight per piece (excluding packing) | 8.06 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# UC-WMTBA (24X5) BU - Cable marker



0820552

<https://www.phoenixcontact.com/us/products/0820552>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Conductor marking |
| Type         | Card form         |

### Marking

|                                     |                   |
|-------------------------------------|-------------------|
| Number of individual labels         | 12                |
| Number of individual labels per row | 4                 |
| Identification technology           | UV LED technology |

### Dimensions

|        |          |
|--------|----------|
| Width  | 24 mm    |
| Height | 10.62 mm |
| Depth  | 4 mm     |

### External dimensions

|                  |                   |
|------------------|-------------------|
| Outside diameter | > 4 mm ... 136 mm |
|------------------|-------------------|

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 24 mm |
| Text field height | 5 mm  |

### Material specifications

|                                                        |                                |
|--------------------------------------------------------|--------------------------------|
| Color                                                  | blue (RAL 5015)                |
| Material                                               | PA                             |
| Flammability rating according to UL 94                 | V2                             |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2                    |
| Components                                             | free from silicone and halogen |

### Cable/line

|                         |           |
|-------------------------|-----------|
| External cable diameter | > 4.00 mm |
|-------------------------|-----------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |

#### Wipe resistance of inscriptions

# UC-WMTBA (24X5) BU - Cable marker



0820552

<https://www.phoenixcontact.com/us/products/0820552>

|                                                 |                                                |
|-------------------------------------------------|------------------------------------------------|
| Specification                                   | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                 | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                  | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed                                    |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |                                               |
|---------------|-----------------------------------------------|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h                                          |

## Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C                                                               |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 2 years                                                                         |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |                          |
|---------------|--------------------------|
| Mounting type | Assembly with cable ties |
|---------------|--------------------------|

# UC-WMTBA (24X5) BU - Cable marker



0820552

<https://www.phoenixcontact.com/us/products/0820552>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UC-WMTBA (24X5) BU - Cable marker



0820552

<https://www.phoenixcontact.com/us/products/0820552>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |
| EF3.0 Climate Change                    |                            |
| CO2e kg                                 | 0.075 kg CO2e              |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)