

Ratings

Voltage: 300 V

Temperature: -80~200 °C

Flammability: VW-1

Oil resistance: 60 °C

≥50% elongation and tensile strength after aging

Conductor

Conductor count: 1

Gauge: 12 AWG 3.3 mm²

Material: tinned copper strands

Strand size: Ø0.47 mm x 19

Resistance at 20 °C: 5.64 Ω /km max

Insulator

Material: Fluorinated ethylene propylene (FEP)

Color: red

Diameter: Ø3.01 ±0.15 mm

Nominal thickness: 0.33 mm

Resistance at 20 °C: 2.5 MΩ /kft min

Wire marking: E339579 UL AWM STYLE 1332 12AWG 200°C 300V



VW-1 --- cUL AWM I A/B 200°C 300V FT1 TENSILITY

Mechanical Tests

After aging at 232±1°C for 7 days

Minimum tensile strength 1.76 kgf/mm²

Minimum elongation 200% original



Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com		
A	05/25/2022	Initial release	Verified:	RoHS compliant Function test: no open, no short circuit, no Intermittent			
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description:	Size:	Part number:	
				Wire, hook-up, TS, 12 AWG, UL 1332, 300V, 200C, 3.01 mm, FEP, red	A	30-02511	
					Scale: 12:1		Sheet 1 of 1

5

4

3

2

1