

C-MOS 3-TERMINAL POSITIVE VOLTAGE REGULATOR

■ GENERAL DESCRIPTION

The NJU7201 series is a C-MOS 3-terminal positive voltage regulator which contains internal accurate voltage reference, error amplifier, control transistor and output voltage setting resistor.

The regulation voltage is fixed by internal circuits and the following line-up of different output voltage versions are available.

The NJU7201 series is suitable for battery operated items and battery back-up systems because of low operating current and low dropout voltage.


■ FEATURES

- Low Operating Current (19µA typ.)
- Wide Operating Voltage Range
- Low Dropout Voltage
 - ($\Delta V_{IO} < 0.3V$ 1.2 to 1.5V output, $I_{OUT} = 0.5mA$)
 - ($\Delta V_{IO} < 0.6V$ 2.5 to 3.5V output, $I_{OUT} = 20mA$)
 - ($\Delta V_{IO} < 0.6V$ 4.0 to 5.5V output, $I_{OUT} = 40mA$)
- Small Temperature Coefficient of Output Voltage
- Output Capacitor 0.1µF Electrolytic Capacitor
- Package Outline (SOT-89)
- C-MOS Technology

■ OUTPUT VOLTAGE LINE-UP

Output Voltage	SOT-89 Type	Output Voltage	SOT-89 Type
+1.2V	NJU7201U12	+3.5V	NJU7201U35
+1.5V	NJU7201U15	+4.0V	NJU7201U40
+2.5V	NJU7201U25	+4.5V	NJU7201U45
+2.7V	NJU7201U27	+5.0V	NJU7201U50
+3.0V	NJU7201U30	+5.2V	NJU7201U52
+3.2V	NJU7201U32	+5.5V	NJU7201U55

■ PACKAGE OUTLINE




NJU7201U (SOT-89)

■ TERMINAL DESCRIPTION

No.	Description
1	GND
2	Input
3	Output

■ EQUIVALENT CIRCUIT



■ ABSOLUTE MAXIMUM RATINGS

(T_a = 25°C)

PARAMETER	SYMBOL	RATINGS	UNIT
Input Voltage	V _{IN}	14	V
Output Voltage	V _{OUT}	V _{IN} +0.3 to GND-0.3	V
Output Current	I _{OUT}	100	mA
Power Dissipation	P _D	300 (SOT-89) *	mW
Operating Temperature	T _{opr}	-25 to + 75	°C
Storage Temperature	T _{stg}	-40 to +125	°C

*) IC Alone

■ ELECTRICAL CHARACTERISTICS

+1.2V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 3.0V, I _{OUT} = 5mA	1.14	1.20	1.26	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 0.5mA	-	0.020	0.30	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 3.0V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 3.0V, I _{OUT} = 1~15mA	-	10	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 1.5~12V	-	0.10	-	%/V

+1.5V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 3.0V, I _{OUT} = 5mA	1.425	1.500	1.575	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 0.5mA	-	0.020	0.30	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 3.0V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 3.0V, I _{OUT} = 1~15mA	-	-	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 1.8~12V	-	0.10	-	%/V

+2.5V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 4.5V, I _{OUT} = 10mA	2.375	2.500	2.625	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 20mA	-	0.20	0.60	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 4.5V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 4.5V, I _{OUT} = 1~20mA	-	-	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 3.5~12V	-	0.10	-	%/V

+2.7V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 4.7V, I _{OUT} = 10mA	2.565	2.700	2.835	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 20mA	-	0.20	0.60	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 4.7V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 4.7V, I _{OUT} = 1~20mA	-	-	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 3.7~12V	-	0.10	-	%/V

+3.0V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 5.0V, I _{OUT} = 10mA	2.85	3.00	3.15	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 20mA	-	0.20	0.60	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 5.0V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 5.0V, I _{OUT} = 1~20mA	-	15	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 4.0~12.0V	-	0.10	-	%/V

+3.2V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 5.2V, I _{OUT} = 10mA	3.04	3.20	3.36	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 20mA	-	0.20	0.60	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 5.2V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 5.2V, I _{OUT} = 1~20mA	-	-	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 4.2~12.0V	-	0.10	-	%/V

+3.5V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 5.5V, I _{OUT} = 10mA	3.325	3.500	3.675	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 20mA	-	0.20	0.60	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 5.5V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 5.5V, I _{OUT} = 1~20mA	-	-	180	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 4.5~12.0V	-	0.10	-	%/V

+4.0V Version

(C_{IN} = C_O = 0.1μF, T_a = 25°C)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	V _{IN} = 6.0V, I _{OUT} = 30mA	3.8	4.0	4.2	V
Dropout Voltage	ΔV _{IO}	I _{OUT} = 40mA	-	0.30	0.60	V
Input Voltage	V _{IN}		-	-	12	V
Operating Current	I _Q	V _{IN} = 6.0V	-	19	30	μA
Load Regulation	ΔV _{OUT} / ΔI _{OUT}	V _{IN} = 6.0V, I _{OUT} = 1~40mA	-	-	120	mV
Line Regulation	ΔV _{OUT} / (ΔV _{IN} · V _{OUT})	V _{IN} = 5.0~12.0V	-	0.10	-	%/V

+4.5V Version

($C_{IN} = C_o = 0.1\mu F, T_a = 25^\circ C$)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	$V_{IN} = 6.5V, I_{OUT} = 30mA$	4.275	4.5	4.725	V
Dropout Voltage	ΔV_{IO}	$I_{OUT} = 40mA$	-	0.30	0.60	V
Input Voltage	V_{IN}		-	-	12	V
Operating Current	I_Q	$V_{IN} = 6.5V$	-	19	30	μA
Load Regulation	$\Delta V_{OUT} / \Delta I_{OUT}$	$V_{IN} = 6.5V, I_{OUT} = 1 \sim 40mA$	-	-	120	mV
Line Regulation	$\Delta V_{OUT} / (\Delta V_{IN} \cdot V_{OUT})$	$V_{IN} = 5.5 \sim 12.0V$	-	0.10	-	%/V

+5.0V Version

($C_{IN} = C_o = 0.1\mu F, T_a = 25^\circ C$)

PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	$V_{IN} = 7.0V, I_{OUT} = 30mA$	4.75	5.00	5.25	V
Dropout Voltage	ΔV_{IO}	$I_{OUT} = 40mA$	-	0.30	0.60	V
Input Voltage	V_{IN}		-	-	12	V
Operating Current	I_Q	$V_{IN} = 7.0V$	-	19	30	μA
Load Regulation	$\Delta V_{OUT} / \Delta I_{OUT}$	$V_{IN} = 7.0V, I_{OUT} = 1 \sim 40mA$	-	35	120	mV
Line Regulation	$\Delta V_{OUT} / (\Delta V_{IN} \cdot V_{OUT})$	$V_{IN} = 6.0 \sim 12.0V$	-	0.10	-	%/V

+5.2V Version

($C_{IN} = C_o = 0.1\mu F, T_a = 25^\circ C$)


PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	$V_{IN} = 7.2V, I_{OUT} = 30mA$	4.94	5.20	5.46	V
Dropout Voltage	ΔV_{IO}	$I_{OUT} = 40mA$	-	0.30	0.60	V
Input Voltage	V_{IN}		-	-	12	V
Operating Current	I_Q	$V_{IN} = 7.2V$	-	19	30	μA
Load Regulation	$\Delta V_{OUT} / \Delta I_{OUT}$	$V_{IN} = 7.2V, I_{OUT} = 1 \sim 40mA$	-	-	120	mV
Line Regulation	$\Delta V_{OUT} / (\Delta V_{IN} \cdot V_{OUT})$	$V_{IN} = 6.2 \sim 12.0V$	-	0.10	-	%/V

+5.5V Version

($C_{IN} = C_o = 0.1\mu F, T_a = 25^\circ C$)


PARAMETER	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	$V_{IN} = 7.5V, I_{OUT} = 30mA$	5.225	5.500	5.775	V
Dropout Voltage	ΔV_{IO}	$I_{OUT} = 40mA$	-	0.30	0.60	V
Input Voltage	V_{IN}		-	-	12	V
Operating Current	I_Q	$V_{IN} = 7.5V$	-	19	30	μA
Load Regulation	$\Delta V_{OUT} / \Delta I_{OUT}$	$V_{IN} = 7.5V, I_{OUT} = 1 \sim 40mA$	-	-	120	mV
Line Regulation	$\Delta V_{OUT} / (\Delta V_{IN} \cdot V_{OUT})$	$V_{IN} = 6.5 \sim 12.0V$	-	0.10	-	%/V

■ CIRCUIT




■ TYPICAL CHARACTERISTICS


Output Voltage vs. Input Voltage




Output Voltage vs. Input Temperature




Output Voltage vs. Input Voltage




Output Voltage vs. Input Temperature









Output Voltage vs. Input Voltage



Output Voltage vs. Input Temperature



■ TYPICAL CHARACTERISTICS



[CAUTION]
The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.