

Halogen-free

REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
B	/	New gold-plated specification	May 2018-11-27	Rain 2018-11-27	Hongkui.liu 2018-11-27
C	/	Add the black housing	May 2020-06-30	Rain 2020-06-30	Hongkui.liu 2020-06-30
D	/	Add gold-plated specification	May 2020-08-21	Rain 2020-08-21	Hongkui.liu 2020-08-21

NOTE:

1.ALL MATERIAL MUST BE COMPLY WITH SS-00259 OR RoHS.

2.PART ON. LEGEND:

F519-1*7*1-110**-E200

NO. OF POSITIONS








7A:2~4um TIN

7Q:GOLD FLASH

7H: 0.05um Au Min.

1A:LCP NATURAL


1B:LCP BLACK




DIMENSION LIST:


NO. OF POS.	A	B	C	NO. OF POS.	A	B	C
3	2.0	4.05	6.8	17	16.0	18.05	20.8
4	3.0	5.05	7.8	18	17.0	19.05	21.8
5	4.0	6.05	8.8	19	18.0	20.05	22.8
6	5.0	7.05	9.8	20	19.0	21.05	23.8
7	6.0	8.05	10.8	21	20.0	22.05	24.8
8	7.0	9.05	11.8	22	21.0	23.05	25.8
9	8.0	10.05	12.8	23	22.0	24.05	26.8
10	9.0	11.05	13.8	24	23.0	25.05	27.8
11	10.0	12.05	14.8	25	24.0	26.05	28.8
12	11.0	13.05	15.8	26	25.0	27.05	29.8
13	12.0	14.05	16.8	27	26.0	28.05	30.8
14	13.0	15.05	17.8	28	27.0	29.05	31.8
15	14.0	16.05	18.8	29	28.0	30.05	32.8
16	15.0	17.05	19.8	30	29.0	31.05	33.8

NO.	COMPONENTS	MATERIALS	FINISH/COLOR SPECIFICATION	QTY
1	Housing	LCP,UL94V-0	NATURAL	1
2	Anchor plate	Brass,T=0.25mm	Surface Plating:2~4um TIN. Under Plating:1~3um Ni	2
3	Contact	PHOSPHOR BRONZE T=0.25mm	Surface Plating:2~4um TIN. Under Plating:1~3um Ni	N




3D_VIEW_REF.

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd			
X.	±0.30	X. °	± 5'			TITLE: Assembly Drawing For FFC/FPC P1.0 NON-ZIF HORIZONTAL TYPE SMT SERIES (BOTTOM CONTACT)			
X.X	±0.25	X.X °	± 4'						
X.XX	±0.20	X.XX °	± 3'	Customer Drw		SIZE PART NUMBER: F519-1*7*1-110**-E200			
X.XXX	±0.15	X.XXX °	± 2'	DRAWN DATE May 2017-12-08					REV. D
LINEAR DIMS		ANGLES DIMS		DESIGN DATE May 2017-12-08		SCALE 5:1 UNIT : mm SHEET 1 OF 2			
DWG NO.: A-S0472				CHECKED DATE Rain 2017-12-08					A4
MATERIAL		SEE NOTES		APPROVED DATE Hongkui.liu 2017-12-08					
FINISHED		SEE NOTES							



DETAIL:A;SCALE 2:1





5. QTY LIST:

DIM	NO.	4~7pin	8~14pin	15&22pin	23&30pin
A		24.00	32.00	44.00	56.00
B		14.20	28.40	40.40	52.40
N		10	8	6	5
TOTAL(PCS)		15,000	12,000	9,000	7,500

NOTES:

- MATERIAL:
 - CARRY TAPE:HIPS,T=0.40mm,CLEAR
 - REEL:HIPS,BLUE.
 - SHIM:PE,CLEAR.
- PRIMARY PACKING:1500PCS/REEL.
- SECONDARY PACKING:"N"REELS/CARTON ("TOTAL"=N*1500/CARTON).
- PEELING RESISTANCE: 0.1N~0.7N(10~70gf);
PEELING ANGLE: 165°~180°;
PEELING SPEED: 300mm/minutes.



UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd			
X	±0.30	X.X	± 5'						
X.X	±0.25	X.X.X	± 4'						
X.XX	±0.20	X.XX.X	± 3'	DOC TYP Customer Drw		TITLE: FPC/FFC P1.0 HORIZONTAL NON-ZIF (BOTTOM CONTACT) SMT TYPE PACKING			
X.XXX	±0.15	X.XXX.X	± 2'	DRAWN DATE May 2017-12-08					
LINEAR DIMS		ANGLES DIMS		DESIGN DATE May 2017-12-08		SIZE PART NUMBER: A4 F519-1*7*1-110**-E200		REV. D	
DWG NO.: A-S0472				CHECKED DATE Rain.Han 2017-12-08					
MATERIAL SEE NOTES				APPROVED DATE Leo.Liu 2017-12-08		SCALE 1:1 UNIT : mm SHEET 2 OF 2			
FINISHED		SEE NOTES							