

**PTFE Spiral Binding for superior protection****SBPTFE**

Wherever superior protection against chemical and extreme temperatures are important, the use of SBPTFE is recommended.


**Features and Benefits**

- Organises and protects cables and hoses
- Excellent fire protection
- Self-extinguishing according to UL94 V0
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters and colours



*Spiral binding SBTPE - ideal for extreme conditions.*

<b>MATERIAL</b>	Polytetrafluoroethylene (PTFE)
<b>Operating Temperature</b>	-60 °C to +260 °C, intermittent +350 °C
<b>Flammability</b>	UL94 V0



*Spiral binding*

<b>TYPE</b>	<b>Nominal Ø</b>	<b>Wall (WT)</b>	<b>Pitch (P)</b>	<b>Bundle Ø min.</b>	<b>Bundle Ø max.</b>	<b>Colour</b>	<b>Reel Length</b>	<b>Article-No.</b>
<b>SBPTFE1.5</b>	1.5	0.50	6.0	1.6	8.0	Natural (NA)	5 m	161-45000
<b>SBPTFE4</b>	4	0.70	7.8	5.0	20.0	Natural (NA)	5 m	161-45100
<b>SBPTFE9</b>	9	1.00	12.5	10.0	100.0	Natural (NA)	5 m	161-45200

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.