

VLT40 Series

40W single and triple output AC/DC Power Supplies

Low profile in a 4.0"x2.0"x1.07" package and over 82% efficient the EOS VLT40 product family comes in single and multiple DC output configurations.

The VLT40 offers a full 40 watts output power with convection cooling and more with optional air flow. A cover kit is available for easy drop in design and manufacturability. This industry and designer's favorite is used to power datacom, industrial, multimedia and many other market segments. If space is a premium and thermal management integral to your design we suggest the VLT40 as the optimum solution. The VLT40 family is RoHs compliant and our factory is ISO 14001 environmentally approved. Worldwide safety standards apply and the power supply is fitted with OVP and OCP standard features.



Model Number	Output	Voltage / Current *	Voltage Set Point	Min. Load
VLT40-1200	V1	5V@8.0A	5. 1V	0. 2A
VLT40-1201	V1	12V@3.5A	12V	0. 1A
VLT40-1202	V1	15V@2.7A	15V	0. 1A
VLT40-1203	V1	24V@1.7A	24V	0. 05A
VLT40-1204	V1	48V@ 0.83A	48V	0.05A
VLT40-3200	V1	5V@6.0A	5. 2V	0. 5A
	V2	12V@2.0A	12. 5V	0. 1A
	V3	-12V@0.5A	-12. 8V	0. 0A
VLT40-3201	V1	5V@6.0A	5. 2V	0. 5A
	V2	24V@1.0A	23. 8V	0. 1A
	V3	-12V@0.5A	-12. 8V	0. 0A
VLT40-3202	V1	5V@6.0A	5. 2V	0. 5A
	V2	15V@1.5A	14. 6V	0. 1A
	V3	-15V@0.5A	-14. 8V	0. 0A
VLT40-3203	V1	3.3V@6.0A	3. 3V	1A
	V2	5V@3.0A	5. 2V	0. 1A
	V3	-12V@0.5A	-12. 8V	0. 0A
VLT60CK		Metal cover kit accessory		

* Maximum current per output channel. Do not exceed total output power rating



Features :

- > 40 W convection cooled rating.
- > Small 4.0"x2.0"x1.07" inch form factor.
- > High efficiency > 82%.
- > Single to triple outputs.
- > Low conducted and radiated noise.
- > Patented resonant topology
- > Cover Kit accessory available.

INPUT SPECIFICATION		
AC Input	Auto Ranging	90 to 132 V 180 to 264V
Efficiency	VLT40-3203 Other Models	75%Typical 82%Typical
Input Frequency		47-63 Hz
Input Current	Full Load at low line	1.1Arms , max
Inrush Current	High Line , cold start	75A, max

OUTPUT SPECIFICATION		
Output Power		40W max
Voltage Set Point		See table
Hold-Up Time	115V/230V	6ms./15ms
Voltage Set Point Accuracy	V1 V2 and V3	±3% ±5%
Line Regulation	Low line to high line	± 0.3%
Load Regulation	Min to 50% & 50% to Max Load V1 V2 and V3	±0.5% ±5%
Transient Response	50% to full load Voltage Deviation Recovery Time	10%, max <5 ms
OVP (For 3 o/p models only)	V1 only 3.3 V V1 only 5V	3.95V, ±0.25V 6.2V, ±0.4V
Overload Protection	Primary limited	Yes, 130%
Short Circuit Protection	Auto recovery <6s	Short Term
Ripple and Noise	3.3V and 5V Other Voltages	50mV 1%
Output Rise Time	All outputs	<100ms

All EOS power supplies have UL, CSA and Nemko safety compliance and medical versions meet UL60601-1 standards. All our products are RoHS compliant. Visit us at www.eospower.com. EOS brand power supplies and patents are owned exclusively by EOS Power. All Rights Reserved.




VLT40 Series

40W single and triple output AC/DC Power Supplies



EMC AND SAFETY SPECIFICATIONS	
CE Mark	Complies with the LVD
EMC	EN5022-B,CISPR22-B, FCC Part 15 Class B, EN50082-1
Agency Approval	VDE , UL, c-UL,NEMKO
Safety Standard	IEC60950, EN60950, UL 60950, CSA 60950 Class 1 SELV C22.2 No.
Safety file number	VDE: 114588 UL: E150565 NEMKO: 29343

ENVIRONMENTAL SPECIFICATION		
Operating Temperature	No derating Linear derate to 50%	0 to 50° C 51 to 70° C
Storage Temperature		-40 to 70° C
Cooling		Convection
Relative humidity	Non condensing	95%, max
MTBF	MIL - HDBK-217F	> 100,000 hrs



OUTPUT CONNECTOR J2		
	Single Output	Triple Output
Pin1	V1	V1
Pin2	V1	V1
Pin3	Common	Common
Pin4	Common	Common
Pin5	NC	V3
Pin6	NC	V2

INPUT SPADE CONNECTOR	
GND	AC Ground

MECHANICAL SPECIFICATION	
AC Input Connector J1	Molex 3 position, 0.156 center Header 26-60-4030 or equivalent
Ground Connector	Spade connector
DC Output connector J2	Molex 6 position, 0.156 center Header 26-60-4060 or equivalent
Size	4.0"x2.0"x1.07"
Weight	5oz (150g)

INPUT CONNECTOR J1	
Pin1	AC Neutral
Pin2	AC Line

All EOS power supplies have UL, CSA and Nemko safety compliance and medical versions meet UL60601-1 standards. All our products are RoHS compliant. Visit us at www.eospower.com. EOS brand power supplies and patents are owned exclusively by EOS Power. All Rights Reserved.

