



## NBNC75BFG7

The rearTWIST HD BNC cable connector offers a true 75  $\Omega$  design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

### Suitable cables:

Argosy Image 360, Belden 1855ENH, Bryant BD SD01, CAE HD0628LSZH, Canford SDV, Canford SDV-LFH, Canford SDV-X-LFH, Cordial CVI 06-28, Cordial CVI 06-28HD, Cordial CVI 06-28HD-FRNC, Cordial CVI 3-7, Draka 0.6/2.8 AF, Draka 0.6 L/2.8 AF, Extron BNC-5RC, Fuzion SD-1, Klotz V06/28, Klotz VMXx75Y, Kabeltronik HFV 0.6/2.8 AF-FRNC, Kabeltronik MVP 5x 0.6/2.8 AF-FRNC, Nexans HF 75 0,6/2,9 02YS(ST)CH, Percon VK5, Quadtronics CABPGHD70MW-500, Sommer 600-0101M, Sommer 600-0104M, Tesca Supra

### Crimp size:

Pin: 1.6 mm (square)

Shield: 5.0 mm (hex)

## Features & Benefits

- ✓ “rearTWIST Principle” locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- ✓ Ideal for recessed bulkheads where access to the “head” of the connector might be an issue. These connectors turn from the back and not the front.
- ✓ True 75  $\Omega$  design meets the stringent HDTV / DVD requirements
- ✓ Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!

- ✓ Snug-fit center pin insert provides tactile feedback
- ✓ Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- ✓ Excellent cable protection and retention
- ✓ Precise Swiss machined brass parts for outstanding durability
- ✓ Accessories include color coded boots in 10 standard colors, crimp tool and dies

## Technical Information

Product	
Title	NBNC75BFG7
Connection Type	BNC 75 $\Omega$
Gender	male

Electrical	
Contact resistance	$\leq 3 \text{ m}\Omega$ (inner)
Contact resistance	$\leq 2 \text{ m}\Omega$ (outer)
Dielectric strength	1,5 kVdc
Impedance	75 $\Omega$
Insulation resistance	$> 5 \text{ G}\Omega$
Rated voltage	$< 50 \text{ V}$
VSWR	$\leq 1.050 / > 32 \text{ dB}$ up to 1 GHz $\leq 1.065 / > 30 \text{ dB}$ up to 2 GHz $\leq 1.100 / > 26 \text{ dB}$ up to 3 GHz

Mechanical	
Cable O.D.	4.7 mm
Cable retention	> 30 N (Center)
Crimp size	5 Hex crimp (shield) acc. MIL22520/5-43(B)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material	
Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental	
Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2