

## Han K 4/0 Pin Female Insert



Image is for illustration purposes only. Please refer to product description.

Part number	09 38 006 2711
Specification	Han K 4/0 Pin Female Insert
HARTING eCatalogue	<a href="https://harting.com/09380062711">https://harting.com/09380062711</a>

### Identification

Category	Inserts
Series	Han-Com <sup>®</sup>
Identification	Han <sup>®</sup> K 4/0

### Version

Termination method	Screw termination
Gender	Female
Size	16 B
Number of contacts	4
PE contact	Yes

### Technical characteristics

Conductor cross-section (mm <sup>2</sup> )	1.5 ... 16 mm <sup>2</sup>
Rated current	80 A
Rated voltage	830 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated current acc. to UL	80 A
Rated voltage acc. to UL	600 V
Rated current acc. to CSA	80 A
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤0.3 mΩ

Page 1 / 3 | Creation date 2026-04-17 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97100 | [electric@HARTING.com](mailto:electric@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)



Pushing Performance  
 Since 1945

## Technical characteristics

Stripping length	14 mm
Tightening torque	1.2 Nm @ 1.5 mm <sup>2</sup> 2 Nm @ 2.5 mm <sup>2</sup> 3 Nm @ 4 mm <sup>2</sup> 3 Nm @ 6 mm <sup>2</sup> 3 Nm @ 10 mm <sup>2</sup> 3 Nm @ 16 mm <sup>2</sup> 0.5 Nm Fixing screws M3 3 Nm Contact screw M6 2 Nm PE screw M5
Recommended screw driver	Slotted 0.6 x 3.5 Slotted 0.8 x 4.5 PH2
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)



**Pushing Performance**  
Since 1945

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	22.748 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140056251
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522