Part Number : 2069583223
Product Description : ConnTAK50 Header, Dual Row, Right-Angle, Surface Mount, 22 Circuits, Key C, Blue
Series Number : 206958
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2069583223_sd.pdf

2069579000-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2046310000-AS-000.pdf

2046310000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	206958
Description	ConnTAK50 Header, Dual Row, Right-Angle, Surface Mount, 22 Circuits, Key C, Blue
Application	Automotive, Wire-to-Board
Component Type	PCB Header
Product Name	ConnTAK50
UPC	195842168817

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	14V AC/DC

Physical

Breakaway	No
Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Blue
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No

Downloaded from Arrow.com.

Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Matte Tin
Material - Resin	High Temperature Nylon
Net Weight	3.060/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Polarizing Ribs
Polarized to PCB	No
Sealed	Unsealed
Shrouded	Shrouded
Temperature Range - Operating	-40° to +100°C USCAR Class T2, -40° to +105°C LV-214
Termination Interface Style	Surface Mount
Terminal Size	0.5

Mates With / Use With

Mates with Part(s)

Description	Part Number
ConnTAK50 Dual Row Tang Receptacles	205825
ConnTAK50 Dual Row Tang Receptacles with CPA	205826

Downloaded from Arrow.com.