



HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)  
TFE-20-X-STK  
[Raychem](#) | [TFE](#)

[TFE-20-X-STK](#)  
TE Internal Number: 5950062006  
Alias ID: 9-1194703-0

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Wall Type** Single
- Resistant To** Fluids, Mechanical Damage
- Low Outgassing** No
- Product Source** Ireland
- Packaging Method** Stick

DOCUMENTATION

Catalog Pages/Data Sheets

**TFE And TFER Pages From 9-1773447-9**  
PDF  
English

**At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8**  
PDF  
English

Product Specifications  
Product Specification

**TFE Sleeving**  
PDF  
English

Instruction Sheets

Global Dimensional Life For RAYCHEM Heat Shrink Tubing Standard Size Products (Customer Distribution)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type Single  
Product Family TFE

Electrical Characteristics

Voltage (Max) (kV) .6

Body Features

Shrink Ratio 1.8:1  
Color Clear  
Flexibility Flexible  
Material Polytetrafluoroethylene (PTFE)  
Fluid Type Chemicals/Solvents, Water

Dimensions

Expanded Inside Diameter (Min) 1.5 mm [ .059 in ]  
Recovered Inside Diameter (Max) 1 mm [ .039 in ]  
Recovered Wall Thickness (Tolerance) .3 mm [ .012 in ]  
Cut Length 1220 mm [ 48.031 in ]

Usage Conditions

Shrink Temperature (Min) (°C) 340  
Resistant To Fluids, Mechanical Damage  
Recovery Temperature (°C) 340  
Operating Temperature Range (°C) -65 – 250  
Flammability Flame-Retardant  
Fluid Resistance Splash Protection

Product Availability

Applicable Region Global

Packaging Features

Packaging Method Stick

Other

Low Outgassing No  
Product Source Ireland



Statement of Compliance

**Statement of Compliance**

PDF

---