



Part Number : [533091670](#)
Product Description : SlimStack Board-to-Board Connector, 0.80mm Pitch, Plug, 5.65mm Mated Height, 16 Circuits, Right-Angle, without Boss
Series Number : 53309
Status : Active
Product Category : Board-to-Board Connectors

Documents & Resources

Drawings

[533091670 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[SPK-53309-001-001.pdf](#)

[PS-52465-014-001.pdf](#)

[PS-52588-031-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	0.8 and above
Description	SlimStack Board-to-Board Connector, 0.80mm Pitch, Plug, 5.65mm Mated Height, 16 Circuits, Right-Angle, without Boss
Application	Board-to-Board, Signal
Component Type	PCB Header
Product Name	SlimStack
UPC	822348124268

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16

Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	None
Mated Height	5.65mm
Mated Width	4.70mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	294.824/mg
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	0.80mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Shrouded	Fully
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.80mm Pitch Vertical SlimStack Receptacles	<u>52465</u>