



A

DETAIL A
TYPE II


9. .050 MAX SOLDER ON INDICATED AREA PERMISSIBLE, FOR -11 AND -12 ONLY.
8. INDICATED AREA SHALL BE CAPABLE OF MEETING THE SOLDERABILITY REQUIREMENTS OF 9-8825 AFTER STEAM AGING.
7. SOLDER ON INDICATED AREA PERMISSIBLE.
6. DIMENTION APPLIES AFTER PRETINNING.
5. PRETIN PER 9-7894 INDICATED LENGTH AFTER PLATING.
4. ALL DIMENSIONS ARE AFTER PLATING.
3. BLACK INK STAMP TRADEMARK 9-6700 TYPE IV, PER 9-7530 IN APPROXIMATE POSITION SHOWN AFTER PLATING. DIRECTION OPTIONAL. TRADEMARK MAY BE SOLID AS SHOWN.

2	GOLD PLATE	9-6800-2
3	GOLD PLATE	9-6800-3
4	GOLD PLATE	9-6800-4
5	GOLD PLATE	9-6800-5
F	GOLD PLATE	9-6800-F
G	GOLD PLATE	9-6800-G
H	GOLD PLATE	9-6800-H
X	GOLD, PALLADIUM, NI	9-9111

1. PROCESS SPEC:
TEST 9-5272-16
NOTES: 9-6700, 9-1180, 9-6800, 9-8825, 9-9111

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

	PRO/ENGINEER INFORMATION
N/A	Pro/e Model Used: 10-497694.ASSEM
NEXT ASSEMBLY	Drawing Name: 10-497694

UNLESS OTHERWISE SPECIFIED		SPECIFICATIONS		POS	QTY	PART NUMBER		DESCRIPTION		NOTE		
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = ±.0005 ANGLES= ±2° .XXX = ±.010 .XX = ±.03 .X = ±.1 ----- DIM. & TOL. PER ASME Y14.5M; DRM PER MIL-DTL-31000; OTHER Amphenol Stds. PER 9-3800 LEGENDS:  -FLAG NOTE CALL OUT REFERENCE ONLY		MATERIAL SPEC.		PARTS LIST								
		N/A		APPROVALS		DATE		AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838 CONTACT, PIN, ELECTRICAL CONNECTOR, SIZE 16, PCB, TYPE JT-R				
				PREPARED BY		06-Feb-03						
				ENGINEER IN CHARGE								
				DESIGN MANAGER								
		PROCESS SPEC.		E. SHEPLER								
SEE NOTE 1		DESIGN ACTIVITY GROUP		MIL/AERO								
		THIRD ANGLE PROJECTION				SIZE		CAGE CODE		DOCUMENT NO.		REV.
						C		77820		10-497694		J
						SCALE: 10.0		REF. 10-497694		SHEET 1 OF 3		

SIZE C	CAGE CODE 77820	DOCUMENT NO. 10-497694	REV. J
SCALE: 10.0		REF. 10-497694	SHEET 1 OF 3

