



REV	DOCUMENT	CHANGED BY	CHECK
5	0041567	JA 14JUL08	ASD



CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	JA	16OCT07	Honeywell					
OPERATING FORCE 3-5 OZ RELEASE FORCE 1 OZ MIN DIFFERENTIAL TRAVEL .004 MAX OVERTRAVEL .010 MIN		CONTACT ARRANGEMENT S P D T					NO PLACES X ± 0.400	CHECK	PSR						16OCT07
		30 VOLTS DC RATING			ONE PLACE .X ± 0.03	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.									
			SEA LEVEL	50000 FT	TWO PLACE .XX ± 0.015										
		INDUCTIVE	3 AMP	2.5 AMP	THREE PLACE .XXX ± 0.005										
		RESISTIVE	5 AMP	5 AMP	ANGLES X ± 3.0°										
		MAXIMUM INRUSH 24AMP			THIRD ANGLE PROJECTION 		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
		APPROVALS	KEMA,CE	5A,250 V ~ T85 IE4  							B	I	-	ISM33-H2	
UL,CSA	5A,250 VAC  		BRAND L4	Pro/ENGINEER 2D				SCALE	-		SHEET	I OF I			