




PRODUCT NUMBER: 1805-0-15-80-43-14-04-0

www.mill-max.com
DATA SHEET



1805-0-15-80-43-14-04-0 SPECIFICATIONS



General Info		Materials	Technical Specs
Description¹: Receptacle With A Standard Tail		Shell Material⁶: Brass Alloy	Mechanical life 1,000 Cycles Minimum (Durability) ⁹ :
Mounting Feature:	Press-Fit into a Non-Plated Through Hole (NPTH)	Shell Plating⁷: 200 - 300 μ " Tin (matte finish) over Nickel	Operating Temperature Range¹⁰: -55/+125° C
Mounting Hole²:	.057" (1,448mm)	Contact Plating⁸: 10 μ " Gold over Nickel	Maximum Current: 8A @ 30° C Temp. Rise
Alternate Mounting³:	Through-Hole Solder tail Mount		Maximum Derated Current: 6.4A
Pin Diameter Range:	.015"-.026" (0,381-0,660mm)		Contact Resistance: 10 m Ω Max
Packaging:	Packaged in Bulk		Shock¹¹: No Elect. Discontinuity > 1 μ s @ 50g
RoHS⁴:	Yes		Vibration¹²: No Elect. Discontinuity > 1 μ s @ 10-2000HZ, 20 G
Product Lifecycle⁵:	Active		
Country Of Origin:	USA		

NOTES:

- 1. Standard Tolerances:
Lengths +/- .005" (0,13)
Diameters: +/- .002" (0,051)
Angles: +/- 2°
- 2. This is a general guideline; your application may require different specifications
- 3. For through-hole solder mounting of this part, the suggestion is to make the finished hole size, at its minimum, .004" larger than the diameter being soldered into the mounting hole.
- 4. Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).
- 5. Part is Active and in Production, No Scheduled Obsolescence
- 6. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
- 7. TIN (100%) per ASTM B 545, Matte finish (With whisker and oxide inhibitors); NICKEL per ASTM B 689, Type 2 (Bright)
- 8. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK {Knoop hardness}), NICKEL per ASTM B 689, Type 2 (Bright)
- 9. Receptacles are capable of 1,000 Minimum insertion/extraction cycles for a broad range of applications. Mating pin size, shape and finish, along with application specific variables, will affect the life of a receptacle contact.
- 10. Per IEC 60512-11-(4,-9,-10,-12)
- 11. Per IEC 60512-6-3: Test 6c: Shock
- 12. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

CONTACT:

#43 CONTACT
FOR .015"-.026" DIAMETER PINS (δ = .008)
6-FINGER (BeCu), GROUP C



The insertion / extraction force characteristics above were derived using a 30 microinch gold-plated contact and polished steel gauge pins having a bullet-shaped tip. The curves represent typical average values; they are best used to compare the differences between similar size contacts and to guide you in selecting one that is suitable for your application. Your results may vary, so for your specification, we encourage you to obtain complimentary samples for your evaluation.

Material	Beryllium Copper	Fingers	6
Compliance (δ)	0.008	Length	.083" (2,108mm)
Maximum Current	8A @ 30° C Temp. Rise	Maximum Operating Temp @ Max Current	120.00° C

20% De-rated Maximum Current	6.40A	Contact Resistance	10.00mΩ Max
Contact Group	C		

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

Engineering Notebook: (<https://www.mill-max.com/engineering-notebooks/pin-receptacles/the-backbone-of-your-interconnect-system>)

Environmental Compliance: (<https://www.mill-max.com/rohs>)