IM06DJR ✔ ACTIVE


Axicom | Axicom IM

TE Internal #: 7-1462039-0

General Purpose Signal Relay, DC, Polarized, Monostable, 2 Form C DPDT-CO, 5 A Contact Rating, 12 VDC Coil Voltage, 250 VAC Contact Voltage, Axicom IM

View on TE.com >

Relays & Contactors > Electromechanical Relays









Relay & Contactor Type: **General Purpose Signal Relay**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **2 Form C DPDT-CO**

Current Type: **DC**

Contact Current Rating: **5 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Signal Relay

Configuration Features

Contact Special Features	Bifurcated/Twin Contacts, J Leg
Relay Options	RF Rated
Contact Number of Poles	2
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Contact Limiting Short-Time Current	5 A
Contact Limiting Making Current	5 A
Contact Limiting Continuous Current	5 A
Contact Limiting Breaking Current	5 A
Insulation Initial Dielectric Between Open Contacts	750 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	750 Vrms
Contact Switching Voltage (Max)	250 VAC

Downloaded from Arrow.com.

Contact Switching Load (Min)	.1mA @ .0001V
Voltage Standing Wave Ration (HF Parameter)	1.06db @ 100MHz, 1.49db @ 900MHz
Coil Resistance	1029 Ω
Insulation Initial Resistance	1000000 MΩ
Contact Current Rating	5 A
Coil Voltage Rating	12 VDC
Contact Voltage Rating	220 VDC
Coil Power Rating DC	.14 W
Insulation Initial Dielectric Between Contacts & Coil	1500 Vrms

Signal Characteristics

Isolation (HF Parameter)	-18.8dB @ 900MHz, -37dB @ 100MHz
Insertion Loss (HF Parameter)	-.03dB @ 100MHz, -.33dB @ 900MHz

Body Features

Product Weight	.75 g[.026 oz]
Enclosure Type	Hermetically Sealed

Contact Features

Contact Plating Material	Gold
Contact Material	AgNi

Termination Features

Main Termination & Connection Type	PCB SMT
Coil Termination & Connection Type	PCB SMT

Mechanical Attachment

Product Mount Type	Board Mount

Dimensions

Product Width	6 mm[.236 in]
Product Length	10 mm[.393 in]
Product Height	5.65 mm[.222 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Environmental Category of Protection	RTV
Environmental Ambient Temperature (Max)	85 °C[185 °F]

Operation/Application

Downloaded from Arrow.com.

Solder Process	Reflow Solder Capable
Performance Type	High Current
Coil Magnetic System	Polarized, Monostable
Current Type	DC

Packaging Features

Packaging Method	Reel

Other

Coil Power Rating Class	≤.15 W
Contact Current Class	>2 – ≤5 A
Height Class (Mechanical)	≤7 mm[≤.276 in]
Length Class (Mechanical)	≤11 mm[≤.433 in]
Width Class (Mechanical)	≤7 mm[≤.276 in]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides


Downloaded from Arrow.com.

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 3-1462039-4
IM06CJR=IM RELAY 140mW12V HDV




TE Part # 5-1462039-6
IM06PGR=IM RELAY 140mW 12V



TE Part # 4-1462037-6
IM06JR=IM RELAY 140mW 12V


Also in the Series | Axicom IM



DC Relays(132)



Electromechanical Relays(132)



General Purpose Signal Relays(132)

Customers Also Bought



TE Part #350783-1
12P UMNL CAP HSG




TE Part #1410946-3
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW

TE Part #1410975-3
MULTIGIG RT2 7RW DC RTM CT



TE Part #1-1462039-8
IM06DGR=IM RELAY 140mW 12V



TE Part #3-1462039-7
IM07DGR=IM RELAY 200mW 24V



TE Part #2013978-1
Mini HDMI, RA, SMT



TE Part #2102772-1
DC, 7Row, Half Left End, MULTIGIG RT 2R



TE Part #5120527-1
1FHP,64,30A/S,S,N,S10,12,13,15

Downloaded from Arrow.com.



TE Part #5352068-1
Z-PACK/A RAF 110P

TE Part #91002-1
TOOL SMALL WIRE INS

Documents

Product Drawings

IM06DJR=IM RELAY 140mW 12V

English

Datasheets & Catalog Pages

Axicom Signal and High Frequency Relays (RF Switches) APPLICATION NOTE #2

English

IM_Datasheet

English

Agency Approvals

VDE Certificate

English

Downloaded from Arrow.com.