



Copyright FCI.



FCIconnect.com





1 | 2



3 |

4

PRODUCT NUMBER	PITCH
YK442xx0x0J0G	9.50 mm



MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 30A / 300V 24A
WITHSTAND VOLTAGE: AC2500V/min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 10.54 Lb-In. / 0.8Nm
WIRE RANGE: 22 - 10 AWG / 22-14 AWG
1) MOLDED PARTS: Thermoplastic, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t
3) TERMINAL SCREWS: STEEL, M3.5
APPROVAL:



DIMENSION

Dim A	N×9.5±1.5
Dim B	(N-1)×9.5

N=Number of poles

Poles	Tolerance
2p-4p	±0.20
5p-8p	±0.25
9p-16p	±0.35
17p-23p	±0.40
24p-30p	±0.50

PART NO.: YK 442xx 0 x 0 J0G

No. of poles
02 2 poles
03 3 poles
... ..
30 30 poles

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified		 MM	title TERMINAL BLOCK			
				angles	X.±0.5		BARRIER TYPE			
				X'±1°	X.XX±0.1		scale			
				dr	EVAN LU	061614		dwg no		sheet 1 of 1
				enr	EVAN LU	061614		YK442xx0x0J0G		size A4
				chr	HANKE FENG	061614		type		
				appd	SHI JUN	061614		CUSTOMER Drawing		
sheet index	revision sheet	A	1							

form: A4mmXLc

1 |

2 |

3 |

4

PDS: Rev :A

STATUS:Released

Printed: Jul 22, 2014