NOTES:

1. MATERIALS AND FINISHES:
   BODY, WASHER, & SHELL - BRASS, SILVER PLATING
   MALE CONTACTS - BRASS, GOLD PLATING
   INSULATORS - PTFE, NATURAL
   SPRING - BeCu, NICKEL PLATING
   GASKET - SILICONE RUBBER, RED
   FERRULE - COPPER, SILVER PLATING

2. ELECTRICAL:
   A. IMPEDANCE: 50 OHM
   B. FREQUENCY RANGE: DC-4 GHz
   C. VSWR(RETURN LOSS): 1.35 MAX.
   D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.

3. MECHANICAL:
   A. DURABILITY: 500 CYCLES MIN.
   B. TEMPERATURE RANGE: -65°C TO 165°C


4. PACKAGING:
   A. QUANTITY: SINGLE PACK
   B. MARKING: PACKAGING TO BE MARKED
      "AMPHENOL RF, 31-6871, AND DATE CODE"

5. CABLE ASSEMBLY INSTRUCTIONS:


   A. TRIM CABLE AS SHOWN
   B. SLIDE FERRULE ONTO CABLE.
   C. INSERT CABLE CENTER CONDUCTOR TO CONTACT UNTIL CONTACT BOTTOMS ON DIELECTRIC.
   D. SOLDER OR CRIMP CABLE CENTER CONDUCTOR TO CONTACT.
   E. WHEN CRIMPING CONTACT TO CABLE, CRIMP WITH AMPHENOL TOOL 227-944 (M22520/5-01) AND DIE SET 227-1221-11 CAVITY 'B' (M22520/5-11, CLOSURE "B" (0.068" HEX)).
   F. INSERT CABLE INTO CONNECTOR WITH BRAID OVER KNURL UNTIL IT BOTTOMS.
   G. CRIMP WITH AMPHENOL TOOL 227-944 (M22520/5-01) AND DIES SET 227-1221-11, CAVITY 'A' (M22520/5-11, CLOSURE "A" (0.213" HEX)).

6 SHOWS CABLE ENTRY DIMENSIONS.

REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MANUFACTURING	15-DEC-20	15459	CJV



RECOMMENDED CABLE STRIPPING DIMENSIONS



SCALE 2.000

MIL-C-39012 INSPECTION

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

THIRD ANGLE PROJ.

REFERENCE	EAR#
M39012/20-0007	9224

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE:

<0.5mm = ±0.05mm	[<0.020 = ±0.002]
>0.5 - 6mm = ±0.1mm	[>0.020 - 0.236 = ±0.004]
>6.00 - 30mm = ±0.2mm	[>0.236 - 1.181 = ±0.008]
>30.00 - 120mm = ±0.3mm	[>1.181 - 4.725 = ±0.012]

ANGLES = ±1°

MATERIAL

ENGINEER: C. VIGORITO
DATE: 02-DEC-19

TITLE: BNC R/A PLUG MIL-CRIMP (CATEGORY C) FOR RG-55, 142, 223, & 400 CABLE

SHEET NO. 2 OF 2 | SCALE: 4.0:1.0

Amphenol RF

SIZE	DRAWING NO.	REV
B	31-6871	A
	ITEM NO. 31-6871	
	PART NO. 31-6871	

Downloaded from Arrow.com.