





REV.	DATE	DESCRIPTION
A	01/25/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
 2. CONTACT PIN TO SOLDER

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex							
7						DRAWN	G.R.S.						01/25/04		
6						CHECKED			PART DESCRIPTION SMA CRIMP PLUG (FOR TIMES LMR–200)						
5						ISSUED									
4	FERRULE	COPPER	GOLD	1		SHEET	1 OF 1		PART NO. 132234						
3	CONTACT PIN	BRASS	GOLD	1											
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 132234.DWG							
1	BODY	BRASS	GOLD	1											
DESCRIPTION					MATERIAL	FINISH	QTY	CAD FILE	C:/132/132234.DWG	REV.	A	SIZE	A	SCALE	NA

SMA CRIMP PLUG
(FOR TIMES LMR-200)

132234