






SECTION "C-C"



NO. OF CKT'S.	DIM. A	DIM. B
1	----------	(4.78±.18) .188±.007
2	(3.96±.13) .156±.005	(8.74±.18) .344±.007
3	(7.92±.13) .312±.005	(12.70±.18) .500±.007
4	(11.89±.13) .468±.005	(16.66±.18) .656±.007
5	(15.85±.13) .624±.005	(20.62±.18) .812±.007
6	(19.81±.13) .780±.005	(24.59±.18) .968±.007
7	(23.77±.13) .936±.005	(28.55±.18) 1.124±.007
8	(27.74±.25) 1.092±.010	(32.51±.30) 1.280±.012
9	(31.70±.25) 1.248±.010	(36.47±.30) 1.436±.012
10	(35.66±.25) 1.404±.010	(40.44±.30) 1.592±.012
11	(39.62±.25) 1.560±.010	(44.40±.30) 1.748±.012
12	(43.59±.25) 1.716±.010	(48.36±.30) 1.904±.012
13	(47.55±.30) 1.872±.012	(52.32±.36) 2.060±.014
14	(51.51±.36) 2.028±.014	(56.29±.41) 2.216±.016
15	(55.47±.36) 2.184±.014	(60.25±.41) 2.372±.016
16	(59.44±.36) 2.340±.014	(64.21±.41) 2.528±.016
17	(63.40±.36) 2.496±.014	(68.17±.41) 2.684±.016
18	(67.36±.36) 2.652±.014	(72.14±.41) 2.840±.016
19	(71.32±.36) 2.808±.014	(76.10±.41) 2.996±.016
20	(75.29±.46) 2.964±.018	(80.06±.51) 3.152±.020
21	(79.25±.46) 3.120±.018	(84.02±.51) 3.308±.020
22	(83.21±.46) 3.276±.018	(87.99±.51) 3.464±.020
23	(87.17±.46) 3.432±.018	(91.95±.51) 3.620±.020
24	(91.14±.46) 3.588±.018	(95.91±.51) 3.776±.020

6442-**N-**-**-**

HOUSING OPTIONS

CODE	HOOKS	SIDE HOOKS	RAMP
BLANK	NONE	NONE	NONE
A	NONE	YES	NONE
R	NONE	NONE	FRICTION
B	NONE	NONE	TYPE B
C	NONE	NONE	TYPE C

VOLTAGE RATING OPTION
BLANK=NONE
V= "250 VAC" ON HOUSING

MAT'L. OPTION
BLANK= MATERIAL A (SEE NOTE 1)

MOLDED VOID CODE
Z=NO VOIDS
A=CKT. 1 VOID,
B=CKT. 2 VOID, ETC.
51=1ST MULTIPLE VOID,
52=2ND MULTIPLE VOID, ETC.

NO. OF CKT'S.

NOTES:
1. MATERIAL A: NYLON 6/6 UL94V-2, COLOR: NATURAL
2. FINISH: N/A
3. THIS PART COMPLIES WITH PRODUCT SPECIFICATION PS-40-02.
4. PACKAGING SPECIFICATION: PK-6442-001
5. HOUSING SHOWN ABOVE IS STANDARD HOUSING WITH NO OPTIONS.
6. THIS HOUSING FOR USE WITH TERMINAL NO..
   45570-*, (18-20 GA.) WITH (3.12)/.123 MAX. INSULATION DIA.
   6838-*, (18-24 GA.) WITH (2.79)/.110 MAX. INSULATION DIA.
   7258-*, (22-26 GA.) WITH (1.65)/.065 MAX. INSULATION DIA.
7. LAST CIRCUIT I.D. NOT PRESENT ON 2-3 CIRCUIT HOUSINGS AND MAY OR MAY NOT BE PRESENT ON 4 CIRCUIT HOUSINGS AND LARGER.
8. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
9. SEE SHEET 2 FOR OPTIONS.
10. TEXT ON PART IS FOR REFERENCE ONLY. TEXT AND TEXT LOCATION MAY VARY DEPENDING ON PART NUMBER AND/OR TOOL.

REV	DESCRIPTION	DRAWN	CHKD	APPR	DATE
J5	NOTE 10 ADDED EC NO: UCP2018-0013	SHWARG			2017/07/28

SH.	REV.
4	J
3	J
2	J5
1	J5

QUALITY SYMBOLS: ▽=0 ▽=0 ▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .010
2 PLACES	± 0.25	± .014
1 PLACE	± 0.36	± ---
0 PLACE	±	±

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM/IN
SCALE: ---
DESIGN UNITS: INCH
THIRD ANGLE PROJECTION

DRAWN BY: POLGAR DATE: 1986/12/03
CHECKED BY: PATEL DATE: 1986/12/03
APPROVED BY: LENZ DATE: 1986/12/03
MATERIAL NO.: SEE CHART


TITLE: KK (3.96)/.156 TRIFURCON CRIMP TERMINAL HOUSING 6442 SERIES

molex


DOCUMENT NO.: SD-6442
SHEET NO.: 1 OF 4
SIZE: D

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


Downloaded from Arrow.com.



STD. RAMP OPTION CODE "R"




SELECTIVE RAMP
OPTION CODE "C"



SELECTIVE RAMP
OPTION CODE "B"


NO. OF CKT'S.	DIM. "C"	DIM. "D"
2	(16.48/15.60) .649/.614	(15.47/15.34) .609/.604
3	(20.45/19.56) .805/.770	(19.43/19.30) .765/.760
5	(28.37/27.48) 1.117/1.082	(27.36/27.23) 1.077/1.072




RECOMMENDED (2.03)/.080 THICK PANEL OPENING.

SIDE HOOKS
OPTION CODE "A"

SECT. "E-E"



MOLDED VOIDS
SEE LEGEND ON SHT. 1
SEE CHART FOR VOID CKT. LOCATIONS



OPT. VOLTAGE RATING

NOTE 10 ADDED
EC NO: UCP2018-0013
DRWN: JS 2017/07/06
CHKD:
APPR: SHWARG 2017/07/28
DESCRIPTION
REV

QUALITY SYMBOLS
▽ =0
▽ =0
▽ =0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .010
2 PLACES	± 0.25	± .014
1 PLACE	± 0.36	± ---
0 PLACE	±	±
ANGULAR ±1/2°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM/IN
SCALE: ---
DESIGN UNITS: INCH
THIRD ANGLE PROJECTION

DRAWN BY: POLGAR 1986/12/05
CHECKED BY: PATEL 1986/12/05
APPROVED BY: LENZ 1986/12/05
MATERIAL NO.: SEE CHART

TITLE: KK (3.96)/1.56 TRIFURCON CRIMP TERMINAL HOUSING 6442 SERIES

molex

DOCUMENT NO.: SD-6442
SHEET NO.: 2 OF 4
SIZE: D

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Downloaded from Arrow.com.

6442-N-*

PART NO.	ENG. NO.	VOIDS
26-03-3011	6442-1-Z	
26-03-3021	6442-2-Z	
26-03-3031	6442-3-Z	
26-03-3041	6442-4-Z	
26-03-3051	6442-5-Z	
26-03-3061	6442-6-Z	
26-03-3071	6442-7-Z	
26-03-3081	6442-8-Z	
26-03-3091	6442-9-Z	
26-03-3101	6442-10-Z	
26-03-3111	6442-11-Z	
26-03-3121	6442-12-Z	
26-03-3131	6442-13-Z	
26-03-3141	6442-14-Z	
26-03-3151	6442-15-Z	
26-03-3161	6442-16-Z	
26-03-3171	6442-17-Z	
26-03-3181	6442-18-Z	
26-03-3191	6442-19-Z	
26-03-3201	6442-20-Z	
26-03-3211	6442-21-Z	
26-03-3221	6442-22-Z	
26-03-3231	6442-23-Z	
26-03-3241	6442-24-Z	
	6442-15-B	2
	6442-9-B	2
	6442-12-F	6
	6442-7-51	1,7
	6442-9-51	1,9
	6442-9-52	2,9
	6442-8-B	2
	6442-8-F	6
	6442-10-D	4
	6442-5-B	2
	6442-10-B	2
	6442-5-C	3
	6442-13-B	2
	6442-11-E	5

6442-RN-*

PART NO.	ENG. NO.	VOIDS
26-03-4011	6442-R1-Z	
26-03-4020	6442-R2-Z	
26-03-4030	6442-R3-Z	
26-03-4041	6442-R4-Z	
26-03-4050	6442-R5-Z	
26-03-4061	6442-R6-Z	
26-03-4070	6442-R7-Z	
26-03-4081	6442-R8-Z	
26-03-4090	6442-R9-Z	
26-03-4101	6442-R10-Z	
26-03-4111	6442-R11-Z	
26-03-4121	6442-R12-Z	
26-03-4131	6442-R13-Z	
26-03-4141	6442-R14-Z	
26-03-4151	6442-R15-Z	
26-03-4161	6442-R16-Z	
26-03-4171	6442-R17-Z	
26-03-4181	6442-R18-Z	
26-03-4191	6442-R19-Z	
26-03-4201	6442-R20-Z	
26-03-4211	6442-R21-Z	
26-03-4221	6442-R22-Z	
26-03-4231	6442-R23-Z	
26-03-4241	6442-R24-Z	
26-03-4043	6442-R4-C	3
26-03-4055	6442-R5-E	5
26-03-4065	6642-R6-E	5
26-03-4086	6442-R8-F	6
26-03-4097	6442-R9-G	7
26-03-4108	6442-R10-H	8
26-03-4120	6442-R12-J	10
26-03-4157	6442-R15-G	7
26-03-4073	6442-R7-C	3
26-03-4094	6442-R9-D	4
26-03-4096	6442-R9-F	6
26-03-4092	6442-R9-B	2
26-03-4064	6442-R6-D	4
26-03-4075	6442-R7-E	5
26-03-4095	6442-R9-E	5
26-03-4085	6442-R8-E	5
26-03-4072	6442-R7-B	2
26-03-4063	6442-R6-C	3
26-03-4062	6442-R6-B	2
26-03-4125	6442-R12-E	5
26-03-4123	6442-R12-C	3
26-03-4076	6442-R7-F	6
26-03-4129	6442-R12-I	9
26-03-4143	6442-R14-C	3
26-03-4093	6442-R9-C	3
26-03-4054	6442-R5-D	4
26-03-4052	6442-R5-B	2
26-03-4103	6442-R10-C	3
26-03-4042	6442-R4-B	2
26-03-4106	6442-R10-F	6
	6442-R12-F	6
26-03-4112	6442-R11-B	2
	6442-R13-B	2
26-03-4175	6442-R17-E	5
26-03-4102	6442-R10-B	2
26-03-4032	6442-R3-B	2
26-03-4082	6442-R8-B	2
	6442-R7-51	1,7
	6442-R9-51	1,9
26-03-4099	6442-R9-52	2,9
26-03-4149	6442-R14-M	13
	6442-R4-A	1
26-03-4152	6442-R15-N	14
	6442-R10-51	1,10
26-03-4083	6442-R-08-C	3

6442-RN-*

PART NO.	ENG. NO.	VOIDS

6442-RND-*

PART NO.	ENG. NO.	VOIDS
	6442-R1D-Z	
26-03-7021	6442-R2D-Z	
26-03-7031	6442-R3D-Z	
26-03-7041	6442-R4D-Z	
	6442-R5D-Z	
	6442-R6D-Z	
26-03-7071	6442-R7D-Z	
	6442-R8D-Z	
26-03-7091	6442-R9D-Z	
	6442-R10D-Z	
	6442-R11D-Z	
26-03-7121	6442-R12D-Z	
	6442-R13D-Z	
	6442-R14D-Z	
	6442-R15D-Z	
	6442-R16D-Z	
26-03-7171	6442-R17D-Z	
	6442-R18D-Z	
	6442-R19D-Z	
	6442-R20D-Z	
	6442-R21D-Z	
	6442-R22D-Z	
	6442-R23D-Z	
	6442-R24D-Z	
26-03-7042	6442-R4D-B	2
26-03-7072	6442-R7D-C	3
26-03-7092	6442-R9D-B	2
26-03-7093	6442-R9D-E	5
26-03-7122	6442-R12D-E	5
26-03-7172	6442-R17D-E	5

6442-BN-*

PART NO.	ENG. NO.	VOIDS
	6442-B1-Z	
	6442-B2-Z	
	6442-B3-Z	
	6442-B4-Z	
	6442-B5-Z	
	6442-B6-Z	
	6442-B7-Z	
	6442-B8-Z	
	6442-B9-Z	
	6442-B10-Z	
	6442-B11-Z	
	6442-B12-Z	
	6442-B13-Z	
	6442-B14-Z	
	6442-B15-Z	
	6442-B16-Z	
	6442-B17-Z	
	6442-B18-Z	
	6442-B19-Z	
	6442-B20-Z	
	6442-B21-Z	
	6442-B22-Z	
	6442-B23-Z	
	6442-B24-Z	

6442-CN-*

PART NO.	ENG. NO.	VOIDS
	6442-C5-Z	
	6442-C6-Z	
	6442-C7-Z	
	6442-C8-Z	
	6442-C9-Z	
	6442-C10-Z	
	6442-C11-Z	
	6442-C12-Z	
	6442-C13-Z	
	6442-C14-Z	
	6442-C15-Z	
	6442-C16-Z	
	6442-C17-Z	
	6442-C18-Z	
	6442-C19-Z	
	6442-C20-Z	
	6442-C21-Z	
	6442-C22-Z	
	6442-C23-Z	
	6442-C24-Z	

UPDATE TITLE
EC NO: UCP2009-3148 2009/07/13
DRWN:MKIPPER 2009/07/13
CHKD:SSOUSEK
APPR:FSMITH 2009/08/05
DESCRIPTION
REV

QUALITY SYMBOLS
▼=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---
ANGULAR ±1/2°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM/IN
SCALE: ---
DESIGN UNITS: INCH
THIRD ANGLE PROJECTION

DRAWN BY: POLGAR DATE: 1986/12/02
CHECKED BY: PATEL DATE: 1986/12/02
APPROVED BY: LENZ DATE: 1986/12/02

TITLE: KK (3.96)/.156 TRIFURCON CRIMP TERMINAL HOUSING 6442 SERIES

MOLEX INCORPORATED

MATERIAL NO.: SEE CHART
DOCUMENT NO.: SD-6442
SHEET NO.: 3 OF 4
SIZE: D

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Downloaded from Arrow.com.