
Multilayer Ceramic Chip Capacitors

CGA8R4NP02J473J320KA

RoHS | REACH SVHC-Free | Halogen Free | Lead Free

TDK item description	CGA8R4NP02J473JT****
Applications	Automotive Grade
Feature	Mid: Mid Voltage (100 to 630V) 150°C: High Temperature Application AEC-Q200: AEC-Q200
Series	CGA8(4532) [EIA 1812]
Status	Production



Images are for reference only and show exemplary products.

PDF file of this page
Buy Now
Contact

Documents
- Catalog
- Specification
- RoHS Certificate
- SVHC/REACH Certificate
- Characterization Sheet
- Promotion Video
- Sample Kits

Technical Support Tools
- S-parameter
- SPICE Netlist (Simple)
- SPICE Netlist (Precision)
- Equivalent Circuit Model

Size	
Length(L)	4.50mm ±0.40mm
Width(W)	3.20mm ±0.40mm
Thickness(T)	3.20mm ±0.30mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	
Recommended Land Pattern (PA)	3.10mm to 3.70mm
Recommended Land Pattern (PB)	1.20mm to 1.40mm
Recommended Land Pattern (PC)	2.40mm to 3.20mm

Electrical Characteristics	
Capacitance	47nF ±5%
Rated Voltage	630VDC
Temperature Characteristic	NP0(0±30ppm/°C)
Q (Min.)	1000
Insulation Resistance (Min.)	10000MΩ


Other	
Soldering Method	Reflow
AEC-Q200	Yes
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	500pcs

Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)


Impedance



ESR




Downloaded from Arrow.com.



CGA8R4NP02J473J320KA


Change settings



CGA8R4NP02J473J320KA

Change settings


Capacitance



CGA8R4NP02J473J320KA

Change settings


DC Bias Characteristic



CGA8R4NP02J473J320KA

Change settings

Temperature Characteristic



CGA8R4NP02J473J320KA(No Bias)

CGA8R4NP02J473J320KA(DC Bias = 315V)

Change settings

Ripple Temperature Rising

no data available

Change settings

Products

» Search by Part No. » Search by Characteristics » Distributor Inventory Check

» Capacitors
» Inductors (Coils)
» EMC Components
» RF Components and Modules
» Voltage / Current / Temperature Protection Devices
» Sensors and Sensor Systems
» Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones
» Transformers
» Ferrites and Accessories
» Noise Suppressing / Magnetic Sheet
» Anechoic Chambers and Radio Wave Absorbers
» Power Supplies
» Magnets
» Flash Storages
» Wireless Power Transfer
» FA Systems
» Transparent Conductive Film
» Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)
» Solar Cells
» Biosensor

Application Guides
Technical Support
Tech Library
Environment
Contact
News
Home

About TDK
TDK Worldwide

Terms of Use Privacy Policy

Copyright(c) 1996-2017 TDK Corporation. All rights reserved.
TDK logo is a trademark or registered trademark of TDK Corporation.

Downloaded from Arrow.com.