

COAXIAL ADAPTER, QMA - SMA, 50 Ohm, plug / jack (male / female)
33_QMA-SMA-50-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
QMA	plug (male)	QMA QLF compliant
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CEECC 22110

Interface and material data		
QMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	32 dB	1.05
4 GHz ... 6 GHz	22 dB	1.17

COAXIAL ADAPTER, QMA - SMA, 50 Ohm, plug / jack (male / female)

33_QMA-SMA-50-1/133_N

Mechanical data	
Weight	0.0067 kg
Mating cycles	100

Environmental data	
Operation temperature	-40 °C ... 85 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84014876	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84014876	33_QMA-SMA-50-1/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2169 / Date of publication: 12.07.2025 / uncontrolled copy