




PRODUCT NUMBER

PITCH

TSxx71xB00J0G

5.00 mm





DIMENSION
N = Number of poles

Dim L	NX5.0
Dim B	(N-1)X5.0
Dim C	(N-1)X5.0
Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.25
13p-18p	±0.30
19p-24p	±0.40

PART NO.: TS xx 71 x B 00J0 G

Solid block	0	Black (RAL9005)	RoHS compliant (lead<4%) In copper Alloy
No. of poles	2	Red (RAL3001/D)	
02 2 poles	3	Orange(RAL2011/P)	
03 3 poles	4	Yellow(RAL1018/A)	
... ..	5	Green(RAL6018/T)	
24 24 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	



Material

- Item ③ Clamp: Brass(CuZn), Nickel plated
- Item ⑤ Terminal screw: Steel Zinc plating "-" slot type
- Item ⑦ Female contact: PhBz, Tin plated
- Item ⑧ Top body: Thermoplastic (UL94V-0)
- Item ⑨ Bottom body: Thermoplastic (UL94V-0)

Electrical cULus/VDE/TUV

- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 15A/17A/15A
- Wire range: 2.5mm²/0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5Lb-In./0.5Nm/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus VDE TÜV

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK
					angles	MM	title
					0.1		TERMINAL BLOCK
					X±0.5		PLUGGABLE PLUG,HOOK ON BACK SIDE,WITHOUT FLANGE
					X.X±0.3		dwg no
					X'±1"		sheet 1 of 1
					dr		size
					ENGR		A4
					ENGR		
					chr		
					appd		
					SHI JUN		
sheet index	revision	A					
	sheet	1					