





PRODUCT NUMBER	PITCH
VMxx75x000J0G	5.00 mm



## Material:

- Item (a) Clamp: Steel zinc plated.
- Item (b) Terminal screw: Steel Zinc plating “-” slot type
- Item (c) Female contact: High conductivity copper Tin plated
- Item (d) Terminal (top body): Thermoplastic (UL94V-0)
- Item (e) Terminal (bottom body): Thermoplastic (UL94V-0)
- Item (f) Clamp cage: Steel Zinc plated

## Electrical cULus/TUV

- Voltage rating: 300VAC/300VAC
- Current rating: 20A/20A
- Wire range: 0.34-2.5mm<sup>2</sup>
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In / 0.4Nm
- Screw: M2.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus TUV

N=NUMBER OF POLES

Dim A=(N-1)×5.00+5.0

Dim B=(N-1)×5.00

POLES	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40

PART NO.: VM xx 75 x 0 00J0 G

Solid block	Color	RoHS compliant (lead<4%)
0	Black (RAL9005)	In copper Alloy
2	Red (RAL3001/D)	
3	Orange(RAL2011/P)	
4	Yellow(RAL1018/A)	
5	Green(RAL6018/T)	
6	Blue (RAL5015/A)	
8	Grey(RAL7035/D)	
9	White(RAL1102)	
C	Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family
Itr	ecn	no	dr	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
				tolerances unless otherwise specified			
				angles	X.±0.5		
					X.X±0.3		
				X.±1°	X.XX±0.1		
				dr	EVIN ZHONG 042114		
				engr	EVIN ZHONG 042114		
				chr	HANKE FENG 042114		
				appd	SHI JUN 042114		
sheet	revision	A					
index	sheet	1					

