Part Number : 757571431
Product Description : MX150 Dual Row Header, Vertical, 6 Circuits, 1.5µm Tin (Sn) Plating, 11.20mm Mating Pin Length, 3.05mm PC Tail Length
Series Number : 75757
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

757571431_sd.pdf

PK-36518-340-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-75757-000-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	75757
Description	MX150 Dual Row Header, Vertical, 6 Circuits, 1.5µm Tin (Sn) Plating, 11.20mm Mating Pin Length, 3.05mm PC Tail Length
Application	Wire-to-Board, Automotive
Comments	3.50 x 6.00mm dual row grid
Component Type	PCB Header
Product Name	MX150
UPC	822350702270

Electrical

Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No

Downloaded from Arrow.com.

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.452/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tube
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.57mm
PC Tail Length	3.05mm
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	1.524µm
Polarized to Mating Part	No
Polarized to PCB	No
Sealed	Unsealed
Shrouded	Unshrouded
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Through Hole
Terminal Size	1.5

Solder Process Data

Max-Duration	15
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	33472

This document was generated on Aug 27, 2026

Downloaded from Arrow.com.