



Each WSU wire wrapping tool wraps, unwraps and even strips the appropriate wire diameter with a unique built-in stripper blade. Ideal for bench use or tool kit in all service and repair applications. In addition to versatility, convenience, and reliability, the WSU Series offers exceptional value.

SPECIFICATIONS	WSU-24M	WSU-26M	WSU-30	WSU-30M	WSU-2224
WRAP TYPE	Modified	Modified	Regular	Modified	Regular
WIRE GAUGE	24 AWG (0.5 mm)	26 AWG (0.40 mm)	30 AWG (0.25 mm)	30 AWG (0.25 mm)	22-24 AWG (0.65-0.50 mm)
TERMINAL HOLE DIA.	0.075" (1.9 mm)	0.075" (1.9 mm)	0.036" (0.91 mm)	0.036" (0.91 mm)	0.075" (1.9 mm)
TERMINAL HOLE DEPTH	1.50" (38.1 mm)	1.50" (38.1 mm)	1.50" (38.1 mm)	1.50" (38.1 mm)	1.50" (38.1 mm)
OUTSIDE DIAMETER	.213" (5.4mm)	.213" (5.4mm)	.125" (3.2mm)	.125" (3.2mm)	.213" (5.4mm)
WRAP POST SIZE	0.045" (1.14 mm)	0.045" (1.14 mm)	0.025" (0.63 mm)	0.025" (0.63 mm)	0.045" (1.14 mm)
FUNCTIONS	Wrap, Unwrap, and Strip	Wrap, Unwrap, and Strip	Wrap, Unwrap, and Strip	Wrap, Unwrap, and Strip	Wrap, Unwrap, and Strip
WEIGHT	0.106 lbs (48.08g)	0.104 lbs (47.17g)	0.076 lbs (34.47g)	0.076 lbs (34.47g)	0.086 lbs (39.01g)
UPC NO.	811490013667	811490013100	811490012172	811490011335	811490010291

MADE FOR LIFE®