

NLV32T-1R2J-EF

**Applications**

Commercial Grade

No Directivity

No Directivity

Feature

Wire Wound

Wire Wound

Ferrite Core

Ferrite Core

Series | Type

NLV32-EF

Status

Production

Brand

TDK

**Size**

Length(L)	3.20mm ± 0.20 mm
Width(W)	2.50mm ± 0.20 mm
Thickness Height	2.20mm ± 0.20 mm
Recommended Land Pattern (A)	1.20mm Nom.
Recommended Land Pattern (B)	2.00mm Nom.
Recommended Land Pattern (C)	2.00mm Nom.

Electrical Characteristics

Inductance	1.2 μ H $\pm 5\%$ at 7.96MHz
Rated Current	390mA
DC Resistance [Typ.]	
DC Resistance [Max.]	750m Ω
Self Resonant Frequency [Min.]	100MHz
Self Resonant Frequency [Typ.]	
Q [Min.]	30 at 7.96MHz
Q [Typ.]	

Other

Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
Soldering Method	Wave (Flow) Reflow Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]
Package Quantity	2000pcs
Weight	0.05g

! Images are for reference only and show exemplary products.







! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

NLV32T-1R2J-EF



Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)





! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

NLV32T-1R2J-EF



Associated Images



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.