



View shown without plastic pin and grounding




PC cord drilling dimensions(after plating)
(thickness 1.60 ±0.25 mm)



SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD PART NUMBER	TIN LEAD PART NUMBER	LEAD FREE PART NUMBER	LEAD FREE PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S80C4G1.00	D09S80C6G1.00	D09S80C4G1.00LF	D09S80C6G1.00LF
15	39.14	33.32	26.32	24.34	19.18	D15S80C4G1.00	D15S80C6G1.00	D15S80C4G1.00LF	D15S80C6G1.00LF
25	53.03	47.04	40.04	38.25	33.12	D25S80C4G1.00	D25S80C6G1.00	D25S80C4G1.00LF	D25S80C6G1.00LF
37	69.32	63.50	56.50	54.71	49.68	D37S80C4G1.00	D37S80C6G1.00	D37S80C4G1.00LF	D37S80C6G1.00LF

Gold flush	0.76 > gold	Gold flush	0.76 > gold
------------	-------------	------------	-------------

Detail of grounding strip



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

mat'l. code	ISO 1302	tolerance	ISO 406	ISO 1001	projection	product family
Ltr ecn no dr date	ISO 1302	tolerance unless otherwise specified	ISO 406	ISO 1001	projection	product family
G BX-17859 MP 2014/06/06	ISO 1302	tolerance unless otherwise specified	ISO 406	ISO 1001	projection	product family
angle linear	0.02°	0.02°	0.02°	0.02°	projection	product family
DR	PERSON	1995/10/30	0.00±0.1	scale 2:1	projection	product family
engr	WITTHUN PAUL	2014/06/06			projection	product family
chr	ALIAS BABU	2014/06/06			projection	product family
apnd	BLU K PAUL	2014/06/06			projection	product family
sheet revision	G				projection	product family
index sheet	1				projection	product family

FCI

dwg no sheet 1 of 1 size

C01-8646-0411 A3

Product Customer Drawing